




Sway Brace Attachment

1001

Technical Features

- Sizes available for bracing pipe (Nominal) : DN65/2 1/2" to DN200/8".
- Pipe size used for bracing : 1"/DN25 and 1 1/4"/DN32.
- Material : Carbon steel.
- Finish : Plain or electrogalvanized.



1 - When used with other Tolco® bracing products.

Sway Brace Attachment - 1001

Physical Data

Nominal (metric)	"A" Pipe Size (inch)	"B" Nom. Bracing (metric)	Pipe Size (inch)	Reference			
				Europe		Asia / America	
				Plain	Electrogalvanized	Plain	Electrogalvanized
DN65	2 1/2"	DN25	1"	2001-02500100	1001250100	2001-02500100	2001EG-02500100
DN80	3"	DN25	1"	2001-03000100	1001300100	2001-03000100	2001EG-03000100
DN100	4"	DN25	1"	2001-04000100	1001400100	2001-04000100	2001EG-04000100
DN150	6"	DN25	1"	2001-06000100	1001600100	2001-06000100	2001EG-06000100
DN200	8"	DN25	1"	2001-08000100	1001800100	2001-08000100	2001EG-08000100
DN65	2 1/2"	DN32	1 1/4"	2001-02500125	1001250125	2001-02500125	2001EG-02500125
DN80	3"	DN32	1 1/4"	2001-03000125	1001300125	2001-03000125	2001EG-03000125
DN100	4"	DN32	1 1/4"	2001-04000125	1001400125	2001-04000125	2001EG-04000125
DN150	6"	DN32	1 1/4"	2001-06000125	1001600125	2001-06000125	2001EG-06000125
DN200	8"	DN32	1 1/4"	2001-08000125	1001800125	2001-08000125	2001EG-08000125

Important Design and Installation Notice

Designed, tested, and approved to be used only with other Tolco® bracing products available from Viking SupplyNet®.

The Sway Brace Attachment is designed to be used in conjunction with Series 900 sway brace attachments all joined together with bracing pipe and installed according to National Fire Protection Association (NFPA) 13 for bracing pipe against sway and seismic disturbance.

Place the Sway Brace Attachment over the pipe to be braced. Slide bracing pipe through both attachment holes so that it extends at least 25mm (1") beyond the last hole. Tighten down the two bolts until the heads bottom out.

The figure 1001 is not intended for use with Fig.907, 4-Way Longitudinal Brace Attachment