




TECHNICAL DATA

PILOT REGULATING FLOW CONTROL TRIM

1-1/2" & 2" (DN40 & DN50) MODEL J
FLOW CONTROL VALVE

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com



This Trim Chart is for use with
the following Viking Trim Sets

Valve Size	Galvanized Trim Part No.	Brass Trim Part No.
1-1/2" & 2" (DN40 & DN50)	14768-1	14768-2

This trim is for use with the following
Release Module Trim Kits

Release Type	Galvanized	Brass
Electric	10830	10832


Note: Nipple lengths for brass trim may vary
from those shown on this Trim Chart.

Note: When viewing this data page online, [blue](#)
text represents hyper links and will open the
appropriate data page when clicked.

Notes: For use with Trim Charts on Page 544 b

General Notes:

- Valve must be trimmed as shown. Any deviation from trim size or arrangement may affect the proper operation of the valve.
- Dimensions in parenthesis are millimeters.
- Viking uses ANSI tee designs (large outlet on run, small outlet on run, side outlet) in all trim call-outs.



Note 1: Release System connection.

Note 2: Alarm Connections: Connect alarm line piping to 3/4" (20 mm) NPT outlet. When using a Water Motor Alarm, a strainer is required. 1/2" (15 mm) NPT outlet is for electric Alarm Pressure Switch.

Note 3: Optional non-interruptible connection for Alarm Pressure Switch to activate electric alarm panel. Note: After the Deluge Valve trips, this location cannot be shut off. Alarms may operate until the outlet chamber of the deluge valve is de-pressurized below the set point of the Alarm Pressure Switch.

Note 4: Viking Drain Check Valve is manufactured with a 0.067" (1.7 mm) orifice to allow alarm line to drain. Do not substitute. Check label for proper orientation.



TECHNICAL DATA

PILOT REGULATING FLOW CONTROL TRIM

1-1/2" & 2" (DN40 & DN50) MODEL J
FLOW CONTROL VALVE

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Refer to page 544a
for General Notes and
Notes 1 through 4.

Order Flow Control Valve
Separately




Figure 1

1-1/2" & 2" Pilot Regulating Flow Control Trim for Model J Flow Control Valve



TECHNICAL DATA

PILOT REGULATING FLOW CONTROL TRIM

1-1/2" & 2" (DN40 & DN50) MODEL J
FLOW CONTROL VALVE

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com




Figure 2 - Installation Dimensions

THIS PAGE
INTENTIONALLY
LEFT BLANK