

File Ex643
Project 91NK8404
Project 92NK8181
Project 92NK4717
Project 92NK22931
Project 93NK11446
Project 94NK6187
Project 98NK11873
Project 99NK39499
Project 01NK33
Project 03NK08138

Issued: April 23, 1992
Revised: October 10, 2003

REPORT

on

SPRINKLERS, AUTOMATIC AND OPEN

Viking Corporation
Hastings, MI

Copyright © 1992 Underwriters Laboratories Inc.

Underwriters Laboratories Inc. authorizes the above named company to reproduce this Report provided it is reproduced in its entirety.

GENERAL

OBJECT:

The object of this investigation was to determine compliance of the Model M extra large orifice upright, pendent and pendent recessed sprinklers with Underwriters Laboratories Inc.'s Standard for Automatic Sprinklers for Fire Protection Service, UL 199, and the National Fire Protection Association's Standard for the Installation of Sprinkler Systems, NFPA 13.

GENERAL

OBJECT:

The object of this investigation was to determine compliance of the SIN's VK531, VK532, VK534 and VK608 extra large orifice upright, pendent and recessed pendent sprinklers with Underwriters Laboratories Inc.'s Standard for Automatic Sprinklers for Fire Protection Service, UL 199, and the National Fire Protection Association's Standard for the Installation of Sprinkler Systems, NFPA 13.

D E S C R I P T I O NPRODUCT COVERED:

Model M extra large orifice pendent and upright sprinklers for a maximum pressure of 175 psig with the following types, styles, orifice sizes, heat responsive elements and temperature ratings.

<u>Issue</u>	<u>Description</u>	<u>Nominal Orifice Size, in.</u>	<u>*Heat Responsive Element Type Size, mm</u>	<u>Temperature Ratings, °F</u>
M 175,	Pendent	0.62	3 mm or 5 mm, extra strong bulb, G5	135, 155, 200 and 286
M 175,	Pendent Recessed	0.62	3 mm or 5 mm, extra strong bulb, G5	135, 155, 200 and 286
M 175, +	Wax-coated	0.62	5 mm extra strong bulb, G5	135, 155, 200 and 286
M 175,	Upright	0.62	3 mm or 5 mm, extra strong bulb, G5	135, 155, 200 and 286

+ - The 286°F Model M wax coated sprinkler uses 200°F wax and is intended for installation where the maximum ambient temperature does not exceed 150°F.

GENERAL CHARACTER:

The Model M extra large orifice pendent and upright sprinkler consists of a brass frame, deflector, compression screw, pip cap, Bellville spring and either a G5, 5 mm, 3 mm or 5 mm extra strong frangible glass bulb in the 135, 155, 175, 200 and 286°F temperature ratings manufactured by E. Job. For the pendent recessed sprinkler, Model E-1 or F-1 escutcheon will be used which is identical to the escutcheon being used with currently Listed Model M (8 mm) glass bulb pendent recessed sprinklers. The sprinkler is available in brass and chrome plated finishes.

USE:

The Model M extra large orifice sprinklers are intended for use with automatic sprinkler equipment as covered by the Standard of the National Fire Protection Association for the Installation of Sprinkler Systems, NFPA 13 and installed in accordance with the manufacturer's installation instructions.

MARKING:

<u>Location</u>	<u>Marking</u>
Wrench Head	"Viking" + and year of manufacture on opposite; model designation.
*Deflector - Pendent	"Pendent", "QR", temperature rating °F and °C, control number, UL in circle symbol.
*Deflector - Upright	"Upright", "QR", temperature rating °F and °C, control number, UL in circle symbol.

C O N C L U S I O N

Samples of the product covered by this Report have been found to comply with the requirements and the products are judged to be eligible for Listing and Follow-Up Service. The manufacturer is authorized to use the Laboratories' Mark on such products which comply with the Follow-Up Service Procedure and any other applicable requirements of Underwriters Laboratories Inc. Only those products which properly bear the Laboratories' Mark are considered as Listed by Underwriters Laboratories Inc.

Report by:
STEVEN J. WISNIEWSKI
Engineering Assistant

Reviewed by:

GEORGE E. LAVERICK
Engineering Group Leader