



VEVXC.EX2800 Gauges, Pressure

[Page Bottom](#)

Gauges, Pressure

[See General Information for Gauges, Pressure](#)

ASHCROFT INC

EX2800

250 E MAIN ST
STRATFORD, CT 06614 USA

"Ashcroft", Bourdon spring type, Model 35-2000A-02L-XUL, size 90 mm with glass or plastic windows, in the following pressure ranges: 0 - 1700 kPa, 0 - 2000 kPa, 0 - 550 - 1700 kPa (retard).

"Ashcroft" Bourdon-tube, indicating pressure gauges, Types 35-W1000A-02L-XUL, 35-W1001-A-02L-XUL, 35-W1005P-02L-XUL, size 90 mm, in the following pressure ranges: 0 - 700 kPa, 0 - 1000 kPa, 0 - 1700 kPa, 0 - 2000 kPa, 0 - 4000 kPa, 0 - 550 - 1700 kPa (retard).

[Last Updated](#) on 2007-12-11

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2008 Underwriters' Laboratories of Canada®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under ULC's Follow-Up Service. Only those products bearing the ULC Mark should be considered to be Listed and covered under ULC's Follow-Up Service. Always look for the Mark on the product.

ULC permits the reproduction of the material contained in the Online Certifications Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories of Canada" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories of Canada®"

An independent organization working for a safer world with integrity, precision and knowledge.





VEVX7.EX5232 Gauges, Pressure Certified for Canada

[Page Bottom](#)

Gauges, Pressure Certified for Canada

[See General Information for Gauges, Pressure Certified for Canada](#)

WIKA INSTRUMENT CORP
1000 WIEGAND BLVD
LAWRENCEVILLE, GA 30043 USA

EX5232

Model 111.10, size 100 mm with dials graduated 0-2000 kpa (0-300psi), 0-2758 kpa (0-400psi) 0-550-1700 kpa (0-80-250psi) (Retard).

[Last Updated](#) on 2009-09-18

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)

© 2012 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2012 UL LLC".