FIG. MT-30 Threaded Mechanical Branch Tee





The MT-30 mechanical tee serves the same function as the MT-1 and MT-8, but uses a steel electro-plated u-bolt to save space and for easier installation in tight places. The MT-30 is ideal for direct connections with sprinkler heads and drop nipples. The MT-90 is the BSPT equivalent.

For the latest UL/ULC listed, LPCB, VdS and FM Approved pressure ratings versus pipe schedule, see www.anvilintl.com or contact your local Anvil Representative.









For Listings/Approval Details and Limitations, visit our website at www.anvilintl.com or contact an Anvil® Sales Representative.

MATERIAL SPECIFICATIONS

HOUSING:

Ductile Iron conforming to ASTM A-536, Grade 65-45-12

U-BOLT & NUTS:

U-bolt is carbon steel SAE J429 Gr. 2, zinc plated complete with hex flanged lock nuts conforming to ASTM A-563 Gr. A or B of SAE J995 Gr. 2.

THREADS:

NPT per ANSI/ASME B1.20.1.

COATINGS:

- ☐ Zinc Electroplated
- ☐ Other available options: Example: RAL3000 or RAL9000 Series

GASKETS: Materials

Properties as designated in accordance with ASTM D-2000.


- ☐ Grade "E" EPDM (Green color code)
 - -40°F to 230°F (Service Temperature Range)(-40°C to 110°C) Recommended for water service, diluted acids, alkalies solutions, oil-free air and many chemical services not involving hydrocarbons, oils
 - NOT FOR USE WITH HYDROCARBONS.


PROJECT INFORMATION	APPROVAL STAMP
Project:	☐ Approved
Address:	Approved as noted
Contractor:	☐ Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

FIG. MT-30 Threaded Mechanical Branch Tee









MT-30 THREADED MECHANICAL BRANCH TEE									
Nominal	0.D.	Hole Dimensions		Max.	Dimensions			Annrox	
Size		Min. Diameter	Max. Diameter	Working Pressure▲	A	В	С	T Take-out	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	In./mm	PSI/bar	In./mm	In./mm	In./mm	In./mm	Lbs./Kg
1 1/4 x 1/2	1.660 x 0.840	13/16	15/16	300	21/8	3½	21/4	1%	0.8
32 x 12	42.4 x 21.3	30	33	20.7	54	89	57.2	42	0.4
11/4 x 3/4	1.660 x 1.050	13/16	15/16	300	21/8	31/2	21/4	1%	0.8
32 x 19	42.4 x 26.7	30	33	20.7	54	89	57.2	42	0.4
11/4 x 1	1.660 x 1.315	13/16	15/16	300	21/4	3½	21/4	1%	1.1
32 x 25	42.4 x 33.7	30	33	20.7	58	89	57.2	41	0.5
1½ x ½	1.900 x 0.840	13/16	15/16	300	21/4	3½	21/4	13/4	0.8
40 x 12	48.3 x 21.3	30	33	20.7	57	89	57.2	48	0.4
1½ x ¾	1.900 x 1.050	13/16	15/16	300	21/4	3½	21/4	13/4	0.9
40 x 19	48.3 x 26.7	30	33	20.7	57	89	57.2	48	0.4
1½ x 1	1.900 x 1.315	13/16	15/16	300	23/8	3½	21/4	13/4	1.1
40 x 25	48.3 x 33.7	30	33	20.7	61	89	57.2	48	0.5
2 x ½	2.375 x 0.840	13/16	15/16	300	21/2	3¾	21/4	2	0.9
50 x 12	60.3 x 21.3	30	33	20.7	64	95	57.2	51	0.4
2 x 3/4	2.375 x 1.050	13/16	15/16	300	21/2	3¾	21/4	2	0.9
50 x 19	60.3 x 26.7	30	33	20.7	64	95	57.2	51	0.4
2 x 1	2.375 x 1.315	13/16	15/16	300	25/8	3¾	21/4	2	1.1
50 x 25	60.3 x 33.7	30	33	20.7	67	95	57.2	50	0.5
2½ x ½	2.875 x 0.840	13/16	15/16	300	23/4	41/4	21/4	21/4	0.9
65 x 12	73.0 x 21.3	30	33	20.7	70	108	57.2	57	0.4
2½ x ¾	2.875 x 1.050	13/16	15/16	300	23/4	41/4	21/4	21/4	0.9
65 x 19	73.0 x 26.7	30	33	20.7	70	108	57.2	57	0.4
2½ x 1	2.875 x 1.315	13/16	15/16	300	21/8	41/4	21/4	21/4	1.1
65 x 25	73.0 x 33.7	30	33	20.7	73	108	57.2	56	0.5

BSP equivalent is available as a MT-90.

Note: Tighten nuts alternately to a recommended torque of 18-22 ft.-lbs. (25-30 Nm) on pipe wall less than schedule 10 (Din 2440) or 23-27 ft.-lbs. (31-37 Nm) on pipe walls schedule 10 (DIN 2440) and above.




For dry pipe systems and freezer applications lubrication of the gasket is required, Gruvlok® Xtreme™ Lubricant is required.

^{▲ –} Working Pressure Ratings are for reference only and based on Sch. 10 and Sch. 40 pipe. For the latest UL/ULC, FM, VdS and LPCB pressure ratings versus pipe schedule, please visit anvilintl.com or contact your local Anvil Representative.







Alignment Align the gasket and fitting above the 1.19" (30mm) pipe hole.

BRANCH SIZE	HOLE SAW SIZE	EQUIVALENT PIPE LENGTH		
Inches (mm)	Inches +1/8, -0 (mm +3, -0)	(see note)		
1	1.19	5		
25	30.23	1.52		

Note: Flow Data is expressed as Feet/Meters of Schedule 40 steel outlet pipe with a "Hazen-Williams coefficient of friction value of 120".



Housing Assembly Attach the U-bolt from the other side and fasten the nuts finger tight.



Tighten Nuts Making sure the fitting is properly located over the pipe hole, use a 9/16" (14 mm) wrench to tighten the nuts alternatively to a recommended torque of 18-22 ft.-lbs. (25-30 Nm) on pipe wall less than schedule 10 (DIN 2440) or 23-27 ft.-lbs. (31-37 Nm) on pipe walls schedule 10 (DIN 2440) and above.

Specified Bolt Torque

Specified bolt torque is for the u-bolt used on SPF® threaded mechanical branches. The nuts must be tightened alternately and evenly until fully tightened.

Caution: Proper torquing of mechanical branch u-bolt is required to obtain specified performance. Over torquing the u-bolt may result in damage to the pipe and/or casting which could result in pipe joint separation. Under torquing the u-bolt may result in lower pressure retention capabilities, lower bend load capabilities, joint leakage and pipe joint separation. Pipe joint separation may result in significant property damage and serious injury.