

Model XT

Water Thermal Expansion Tank

Application

Designed for installation on potable water lines between the backflow preventer or pressure reducing valve and the water heater to protect against water thermal expansion. When system pressure increases, water enters the tank's polypropylene lined water chamber which expands a diaphragm into a pre-charged air chamber, keeping system pressure below the relief valve setting.

Standards Compliance

- IAPMO® Listed
- Water Quality Association Certified to NSF/ANSI 61 & 372*
 *(0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

Materials

Outer shell Carbon Steel

Coatings Epoxy finish (outer shell)

Connection Stainless Steel
Liner Polypropylene
Diaphragm Butyl Rubber

Features

Sizes (liters): 8, 18, 35

Maximum working water pressure: 150 PSI

End connections Threaded NPT

ANSI B1.20.1

Factory Pre-charge (adjustable) 40 PSI

Note: Model XT tanks are certified to NSF 61 domestic hot, but are suitable for temperatures up to 200° F.




_						_		
Λ	^	~	0	SS	^	ri	_	0
_	•		_	33	•		ㄷ	3

☐ NR3XL - Water pressure reducing valve☐ TP1100A - Temperature & pressure relief valve

P1000AXL- Pressure relief valve
P3000Cl - Pressure relief valve
P3000BR - Pressure relief valve

975XL2 - Reduced pressure backflow preventer

□ VR10XL - Vacuum relief valve



Dimensions & Weights (do not include pkg.)

TANK DIMENSIONS AND CAPACITIES									
	MAXIMUM	TANII	MAXIMUM	EACTODY					
MODEL		TANK VOLUME (gallons)	ACCEPTANCE VOLUME (gallons)	FACTORY PRE-CHARGE psi	DIAMETER A	HEIGHT B	SYSTEM CONNECTION C	WEIGHT lbs.	
XT-8	150	2.1	1.0	40	8	10 1/2	3/4NPT	5.5	
XT-18	150	4.8	2.4	40	11	13 1/2	3/4 NPT	10	
XT-35	150	9.0	4.25	40	12 1/2	17 1/4	3/4 NPT	15.5	

Zurn Industries, LLC | Wilkins

1747 Commerce Way, Paso Robles, CA U.S.A. 93446 Ph. 855-663-9876, Fax 805-238-5766

In Canada | Zurn Industries Limited

3544 Nashua Drive, Mississauga, Ontario L4V 1L2 Ph. 905-405-8272, Fax 905-405-1292


Rev. A
Date: 6/13
Document No. WXT-XT
Product No. Model XT

Sizing Ch	ıart
-----------	------

Supply	WATER HEATER CAPACITY (U.S. gal)										
Pressure (psig)	20	30	40	50	60	80	100	120	150	175	200
40	8	8	8	8	8	18	18	18	35	35	35
50	8	8	8	8	8	18	18	18	35	35	35
55	8	8	8	8	8	18	18	18	35	35	35
60	8	8	8	8	18	18	18	18	35	35	35
70	8	8	8	18	18	18	18	35	35	35	35
80	8	8	18	18	18	18	35	35	35	35	35
90	8	18	18	18	18	35	35	35	35		
100	18	18	18	18	35	35	35				
110	18	18	35	35	35						
120	35	35	35								
= See WXTP Spec Sheet											

Typical Installation

Local codes shall govern installation requirements. Unless otherwise specified, the assembly shall be mounted on the cold water supply and at least 18" from the cold water inlet to the heater. **Note:** Pre-charge should be adjusted to match incoming water pressure (adjust pre-charge with no water pressure in tank). Not to exceed 80psi.



Model XT Installation

Specifications

The Water Thermal Expansion Tank outer shell shall be carbon steel. The diaphragm shall be FDA approved butyl rubber and, the water chamber shall be polypropylene lined to preclude water contact with the shell interior. The assembly shall have a NPT Stainless steel system connection and a 0.301"-32 charging valve connection (standard tire valve) to facilitate the onsite charging of the tank to meet system requirements. The tank shall be IAPMO® listed and certified to NSF/ANSI 61& 372. The Water Thermal Expansion Tank shall be a ZURN WILKINS Model XT.

Page 2 of 2

Based upon 100° temperature rise (40°F to 140°F)

www.zurn.com

In Canada | Zurn Industries Limited

³⁵⁴⁴ Nashua Drive, Mississauga, Ontario L4V 1L2 Ph. 905-405-8272, Fax 905-405-1292