

Fig. 58 - Threaded Side Beam Bracket

Size Range — 3/8" rod, pipe sizes 1/2" thru 4"

Material - Carbon Steel

Function — Practical and economical bracket used to support piping from wood, concrete or steel beams.

Features — Unique design allows rod to be easily threaded into bracket. Offset design permits unlimited rod adjustment. Center mounting hole will accept 3/8" and 1/2" fastener bolts. Per NFPA 13: 1/2" thru 2" pipe requires 3/8" fastener, 2½" thru 4" pipe requires 1/2" fastener.*

Approvals — Underwriters' Laboratories Listed in the USA **(UL)** and Canada **(cUL)**, and Factory Mutual Engineering approved thru 4" pipe.

*Note — Additionally **UL** has listed the Fig. 58 with fasteners as shown in table below.

Finish - Plain

Note — Available in Electro-Galvanized finish.

Order By - Figure number and finish

UL Listed Fastener Table							
Pipe Size	Qty.	Fastener Type	Material				
2	2	#16 x 2 Drive Screws	Wood				
2	1	3/8 Lag Bolt	Wood				
21/2 - 4	1	1/2 Lag Bolt	Wood				
31/2	2	1/4 x 11/2 Lag Bolt	Wood				
4	2	1/4 x 2 Lag Bolts*	Wood				
4	2	1/4 x 1 tek screws	14 gauge				
4	2	1/4 x 1 tek screws	16 gauge				

^{*} No pre-drilling required

Dimensions • Weights								
Pipe Size	Rod Size	Α	В	С	Max. Rec. Load Lbs.*	Approx. Wt./100		
1/2 thru 4	3/8	23/4	1 ½	1 1/8	300	14		

^{*} With safety factor of 5.



