


	TECHNICAL DATA	6" MODEL G6000 DRY VALVE FRICTION LOSS CHART
---	-----------------------	---

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
 Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
 Visit the Viking website for the latest edition of this technical data page: www.vikinggroupinc.com

FOR USE WITH ENGLISH PRACTICAL SYSTEM
 Where Flow is Measured in GPM and Pressure is Measured in PSI

Graph is for reference purposes.



Friction Loss for the 6" Viking Model G6000 Dry Valve is equivalent to 44.88 feet of 6" Schedule 40 (id = 6.07") Pipe (C = 120).

To calculate friction loss for the 6" (id = 6.07") Viking Model G6000 Dry Valve at a specific flow, use the following formula:

$$P = \left(\frac{4.52 \times Q^{1.85}}{C^{1.85} \times 6.07^{4.87}} \right) \times 44.88$$

PSI

Where P = Friction Loss (PSI)
 Q = Flow in GPM
 C = Constant (=120)