




Trusted above all.



VSN 1230 Suppression Systems

Product Brochure | ASIA



Fire protection

Efficient and compact



VSN 1230 fire extinguishing systems fight fires using FK5-1-12 or Novec™ 1230 by 3M™. This extinguishing agent is particularly suitable for the protection of spaces with electronic and electrical equipment and offers an economical fire protection solution especially for small and medium-sized rooms. The 50 bar technology of the VSN 1230 system makes optimal use of the characteristics of this extinguishing agent.

FK 5-1-12 and Novec 1230 extinguishing agent reduces the heat of the fire and thus stops the combustion reaction. It is very efficient yet unaggressive at the same time.


The extinguishing agent is stored as a liquid and transforms into a gas only when it exits from the extinguishing nozzles. It therefore extinguishes, as a rule, even concealed fire sources instantaneously. The rapid extinguishing of a fire already in the nascent phase minimizes the fire damage and prevents long downtimes or business interruptions.

Furthermore, unlike the case of water, foam or powder secondary damage caused by the extinguishing agent itself is practically impossible. FK 5-1-12 and Novec 1230 are neither corrosive nor electrically conductive, leaves no residue and can easily be removed from the space concerned through ventilation. FK 5-1-12 and Novec 1230 is the preferred extinguishing agent for electronic and electrical risks.

These fire extinguishing systems already achieve their extinguishing effect at a substantially lower design concentration than that of inert gas extinguishing systems. This means that in the event of fire, less extinguishing agent must be introduced, which in turn makes it possible to implement shorter flooding periods. In addition, the pressure relief valve can be made significantly smaller, in most cases.

Furthermore, the comparatively small quantity required for use is stored in liquid form. This allows for extremely compact storage of the extinguishing agent. In addition, in the design concentration of FK 5-1-12 and Novec 1230 does not present any health hazard, which is why these installations are also suitable for areas that are accessed by people.

FK 5-1-12 and Novec 1230 fluid has the best environmental properties, compared to other gaseous chemical extinguishing agents. It does not produce any hazard for the ozone layer and has a very low global warming effect. Within a mere five days, it dissipates completely.



Gas | VSN1230 | 06-07-2023 | Rev - 1.2

In addition to the operating pressures of conventional fire extinguishing systems of 25 bar and 42 bar, VSN 1230 systems are also available in a 50 bar configuration. This offers some significant advantages. For example, they can be adapted individually and tailored specifically to the requirements of the protected area.

Longer pipelines

The regulations for fire extinguishing systems using these agents require that the protected area be flooded within a maximum of 10 seconds. The 50 bar technology makes it possible to use longer and more complex piping than systems using lower operating pressures. This means that the extinguishing agent can also be stored outside the protected area.





This option has the following advantages:

- In the event of fire, the extinguishing system itself is not exposed to fire.
- The space in the protected area can be used for its actual purpose, e.g. for additional server cabinets in the server room.
- The stock of extinguishing agent can be serviced quickly and easily without having to enter sensitive areas.

Multi-zone systems

With 50 bar technology, it is possible to set up one multi-zone system instead of several single-zone systems. Multi-zone systems jointly use a single stock of extinguishing agent for all rooms, while in the case of single-zone systems, a separate storage facility must be provided for each room. This lowers costs and saves space, especially if several rooms of a similar dimension have to be protected in a building.




VSN 1230 fire extinguishing systems can be designed for use as a single-zone system to protect a single protected area or in the form of a multi-zone system to protect two or more areas.

Single-zone systems

A pipework system installed with VSN 1230 extinguishing nozzles is installed in the protected space, while the dimension of the pipework, along with the number and layout of the extinguishing nozzles, is determined by the risk concerned and the specific local conditions. The extinguishing agent is stored in liquid form in special cylinders, where a nitrogen cushion is superimposed over the extinguishing agent and thus generates the operating pressure of 42 or 50 bar.

To protect smaller rooms, a single cylinder is often sufficient. Multi-cylinder systems are used to protect larger rooms.


Smoke detectors continuously monitor the extinguishing zone and send a signal to the fire detection and extinguishing control panel in the event of a fire. In the case of single-cylinder systems, the control panel then opens the electrical valve of the extinguishing agent cylinder to release the agent into the pipework. In the case of multi-cylinder systems, the first cylinder is electrically activated and through the nitrogen



cushion in this first cylinder, the other cylinders are triggered pneumatically. At the same time the fire detection and extinguishing control panel triggers an audible and visual alarm, whereby persons present will be asked to leave the room.

At the same time, it transmits a signal to a permanently manned station. After expiry of a predetermined warning time, the extinguishing process starts: The extinguishing agent is carried through the pipework into the extinguishing zone within 10 seconds.

- | | |
|---|----------------------------------|
| 1. VSN 1230 extinguishing agent cylinder | 4. Flash |
| 2. Fire detection and extinguishing control panel | 5. Fire detector |
| 3. Electric horn | 6. VSN 1230 extinguishing nozzle |
| | 7. Pressure relief flap |




Multi-zone systems

Multi-zone systems are very similar to single-zone systems, except that they use a common stock of extinguishing agent to protect all rooms. In the event of a fire, the fire detection and extinguishing control panel controls specific selector valves. These valves release the extinguishing agent only into the extinguishing zones affected by the fire.

The required quantity of extinguishing agent is always calculated in relation to the largest protected space. If a smaller space is affected by the fire, only as much extinguishing agent as is required is released to extinguish the fire in this space. Due to the reserve of extinguishing agent, the fire extinguishing capacity of the system is guaranteed even after the extinguishing system has been triggered - providing continuous, uninterrupted operation.

Fire detection and extinguishing control technology

The control and function monitoring capacity of VSN 1230 fire extinguishing systems should be provided ideally by the tried and tested Viking FMZ 5000 detection alarm and extinguishing control technology. This ensures optimal compatibility – supported by relevant certifications – of electrical and mechanical system components and avoids unnecessary coordination expense and interface problems between different system parts.




In the pipework, a two-phase flow - composed of liquid Novec 1230 and gaseous nitrogen – is generated after activation of the extinguishing system; this presents a particular challenge for the hydraulic calculation when planning the system.

VSN 1230 fire extinguishing systems are designed for specific projects with the Viking Design Manager. This design programme is based on a specially developed simulation model for the two-phase flow, which has been verified in numerous flow tests on extinguishing system models.


Thanks to the calculation accuracy of the Viking DesignManager, extinguishing systems can be optimally designed - both as regards safety systems and from an economic perspective: the designed extinguishing systems have been proven to be dependable and effective. Unlike conventional design programmes, the Viking DesignManager is also able to include zone distributors of multi-zone systems with up to 15 outlets in the calculation. It also calculates complex and asymmetric pipework, thus offering more flexibility in the system design.

Whether a 50 bar, 42 bar or 25 bar system, single or multi-zone, symmetric or asymmetric pipework – Viking DesignManager will always find the ideal system version and solution for each project.



To further ensure safety in the design of the system, the guided menu of the Viking DesignManager is designed so as to perform an error and plausibility check even while the basic data are entered into the system.

Another highlight: An interface to the AutoCAD software integrated into the Viking DesignManager offers a convenient design of the installation and makes it possible to import the result into the project documents and system records afterwards.



Applications

A class on its own

VSN 1230 fire extinguishing systems are particularly suitable for the protection of spaces with electrical and electronic facilities, even if people are present in the premises.

All system variants and options of the VSN 1230 fire extinguishing systems, including the Viking DesignManager, are UL-listed, FM-approved and tested and certified by VdS Schadenverhütung. Approvals by other international certification bodies are also available.



Examples of use:

- Server rooms and other IT facilities
- Data archives
- Telecommunications equipment
- Control rooms and control stations
- Instrumentation and control rooms
- Electrical switch rooms
- Switchgear and distribution cabinets


Benefits

At a glance


There are many reasons for choosing a Viking VSN 1230 fire extinguishing system:

- The systems provide an excellent extinguishing effect in rooms with electronic and electrical equipment.
- The Novec 1230 extinguishing agent is neither corrosive nor electrically conductive, leaves no residue and can easily be removed from the space in question through ventilation.
- The Novec 1230 extinguishing agent is also very suitable for zones that are frequented by people and has a very high environmental compatibility.
- Operating pressures up to 50 bar allow for more extensive pipework and storage of the extinguishing agent outside the protected area.
- Through cost-effective multi-zone systems, a single stock of extinguishing agent is sufficient to cover several zones.
- The Viking DesignManager calculates complex, asymmetrical pipework automatically and delivers optimal solutions - both from a safety-related and an economic perspective.


VSN 1230 50 bar technology
- makes it possible to use long pipeworks



VSN 1230 Multi-zone technology
- saves space and extinguishing agent



Viking DesignManager
- calculates the optimal solution



For further information, please contact your local Viking sales office or refer to the technical documentation. The contents of this publication are subject to modifications without notice.


Photos
Cover: Fotolia, Minimax AG
Page 3: Minimax AG
Page 7: Minimax AG/DLR/Fotolia

NOTE

PRODUCTS & SOLUTIONS

To address a wide spectrum of fire risk and challenges, Viking offers a broad and comprehensive range of products, systems and solutions classified into these four productgroups:

- **Water** - Water based fire suppression technologies
- **Foam** - Foam based fire suppression technologies
- **Gas** - Gaseous and clean agent based fire suppression technologies
- **Fire Alarm & Detection** - Fire detection and warning technologies



VIKING ASIA NETWORK

Viking relies on a vast network of distributors and resellers across Asia to effectively serve the market. Contact the Viking Office nearest to you and we shall connect you with a distributor nearest your location.



SINGAPORE (Asia Headquarters)

The Viking Corporation (Far East) Pte Ltd

69 Tuas View Square

Westlink Techpark

Singapore 637621

Tel: (+65) 6278 4061

Fax: (+65) 278 4609

Email: VikingAPAC@vikingcorp.com

CHINA

Viking Fire Protection Equipment Trading (Shanghai) Co. Ltd.

Room 507-511, Fourth Floor, Building A

No. 801, Zhujin Road

Songjiang District

Shanghai 201615

China

Tel: (+86) 21 5774 0775

Fax: (+86) 21 5776 0329

Email: XZHANG@vikingcorp.com

HONG KONG

Viking Supply Network (HK) Limited

Unit C, 6th Floor,

Gee Hing Chang Industrial Building

No. 16 Cheung Yue Street

Cheung Sha Wan, Kowloon,

Hong Kong

Tel: (+852) 2391 1078

Fax: (+852) 2787 6063

Email: KYIM@vikingcorp.com

INDIA

Viking Fire Products (India) Pvt. Ltd.

SRS Tower, Office No.137-138

1st Floor, Main Mathura Road

(Near Metro Station Mewla Maharajpur)

Faridabad – 121003, Haryana, India

Tel: (+91) 129 298 2313

Email: SGUPTA@vikingcorp.com

JAPAN

The Viking Corporation (Japan)

AIOS Gotanda Ekimae Building 4th Floor

1-11-1 Nishigotanda, Shinagawa-ku

Tokyo 141-0031,

Japan

Tel: (+81) 3 6303 9571

Fax: (+81) 3 6303 9572

Email: KYOSHIMASU@vikingcorp.com

KOREA

Viking Korea Limited

#71 Gunpo-Ro, Gunpo-City

Gyeonggi-Do

Korea 15888

South Korea

Tel: (+82) 31 502 2510

Fax: (+82) 31 438 0137

Email: JHwang@vikingcorp.com

Trusted above all.