




Trusted above all.™

Healthcare Facilities

Fire Protection and Suppression

Viking's wide range of fire protection and suppression products ensures that even the most critical applications, such as health care facilities, imaging technology rooms, surgical environments and more, are well protected.

Our product breadth and innovation, unmatched quality and our global network ensure that we have what you need, when you need it. Visit **supplynet.com** to place an order today!



ENT Coated Sprinklers and VACTEC for Parking Garages

We offer products like Viking's stainless steel VK368, a small, solder link standard spray sprinkler that can withstand harsh corrosive environments, and FireFlex's VACTEC, a complete FM Approved integrated system that offers unique features and benefits, such as corrosion mitigation measures and system configuration flexibility.



Institutional Sprinklers for Psychiatric Units

Viking's Institutional Sprinklers are small, flush, solder link and lever sprinklers made with tamper-resistant construction. They've been specifically designed for use with concealed piping in institutional mental health occupancies, correctional facilities, or anywhere a likelihood of tampering with fire sprinklers by the occupants may exist.



Concealed Sprinkler Cover Plates for Clean Room Applications

Viking offers a selection of clean room cover plates for clean room approved concealed sprinklers. Our high quality products and unique designs ensure that virtually every clean room application is well protected.






MRI Equipment Approved Products

Viking offers a quick response concealed sprinkler specifically made from non-magnetic materials that are acceptable for use in a high magnetic field environment like those associated with MRI systems. Oxeo Extinguishing Systems, Viking's inert gas suppression system for sensitive applications, and VESDA in conjunction with Viking BlazeMaster™ CPVC pipe are important Viking offerings that protect these environments.



Window Sprinklers for Window Protection

Viking Specific Application window sprinklers are quick response glass bulb, automatic sprinklers. Both Pendant Vertical Sidewall (VSW) and Horizontal Sidewall (HSW) versions are available to meet design needs. In addition to brass and chrome, Polyester and corrosion-resistant Electroless Nickel PTFE (ENT) finishes are available.



SFFF Foam Suppression Systems

The complete foam packages includes ARK and USP 3% SFFF foam concentrates, bladder tanks, and various foam discharge devices including Viking sprinklers and much more.



Hyperbaric Chamber Equipment Protection

Deluge systems are commonly used where it is desirable to simultaneously spray water from all open sprinklers and/or nozzles on the system when the system operates. VXD and Viking Legacy deluge systems can ensure that applications requiring deluge systems are well-protected.



Oxeo Extinguishing Systems

cULus Listed Oxeo extinguishing system uses inert gases Nitrogen and Argon to protect high-challenge applications such as data centers or server rooms without the risk of secondary damage and with no environmental impact. This solution is excellent for Class A-C fires, with Argon being especially useful for Class D fires. It also allows gas to be extracted once the fire is suppressed, making entry into enclosed facilities/rooms safe again.

