

# GRUVLOK<sup>®</sup> FIRE-RITE<sup>™</sup> SHORT PATTERN FITTING SYSTEM

The Gruvlok<sup>®</sup> Fire-Rite<sup>™</sup> short pattern fitting system incorporates 90° elbows and tees in 2" to 8" size range with a 300 psi pressure rating.

Fire-Rite<sup>™</sup> fittings are painted to industry specification and are available galvanized for more corrosive environments.

CAD design increases internal diameters and provides superior flow capability.

Fire-Rite<sup>™</sup> fittings are cast from ASTM A-536 Ductile Iron to Grade 65-45-12.

## Fire-Rite<sup>™</sup> – Light Weight – Heavy Value!

LISTED For Listings/Approval Details and Limitations, visit our website at www.anvilintl.com or contact an Anvil<sup>®</sup> Sales Representative.

— Available galvanized. \* When ordering, refer to product as FP7450.

## MATERIAL SPECIFICATIONS

### **CAST FITTINGS:**

Ductile Iron conforming to ASTM A-536

### COATINGS:

 Rust inhibiting paint Color: ORANGE (standard) or Hot Dipped Zinc Galvanized conforming to ASTM A-153 (optional) Conter available options: Example: RAL3000 or RAL9000 Series



Additional sizes available, see Gruvlok Catalog or contact an Anvil Representative.

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	
FP-4.12	



FIGURE 7450 90° ELBOW			
Nominal Size	0.D.	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	In./mm	Lbs./Kg
2	2.375	23⁄4	1.7
50	60.3	70	0.8
21/2	2.875	3	2.6
65	73.0	76	1.2
3	3.500	33%	3.5
80	88.9	86	1.6
4	4.500	4	6.5
100	114.3	102	3.0
6	6.625	51/2	14.8
150	168.3	140	6.7
8	8.625	61/8	25.6
200	219.1	175	11.6



