



Trusted above all.™

Viking Plastics


Connecting with confidence



The Viking Plastics Supply Chain



Manufacturing



Warehousing



Delivery

Vertical Integration for Quality from Start to Finish

You want the confidence that comes from knowing that nothing is left to chance. When you install CPVC sprinkler piping from Viking Plastics, you are assured of quality in every link of the supply chain. We partner with BlazeMaster®, the proven leader in CPVC compound technology, to deliver products that meet the requirements of the industry's most demanding testing and standards agencies: UL, FM, ASTM, NSF, ANSI, and the Plastic Pipe Institute.

Viking is the only 100% vertically integrated sprinkler systems manufacturer, fabricator, and distributor in the United States. We understand the importance of CPVC material compatibility, and product dependability is a major focus for everyone in the Viking supply chain.

The Viking Plastics Difference

- Protected by industry-leading CPVC compatibility program — Lubrizol's FBC System Compatible program
- Access to training for CPVC installation guidelines, techniques, and best practices
- Product consistency throughout our network of Viking SupplyNet locations
- Vertical integration means Viking is your single source for CPVC pipe manufacturing, distribution and technical support




BlazeMaster is the first and only fire sprinkler CPVC that meets the ASTM 4120-06 material classification with a pressure/temperature rating of 100 psi at 180° F.

Aspirating Smoke Detection (ASD) Pipe

Installation and System Maintenance is Easier Than Ever With ASD Pipe

Viking's UL Listed Aspirating Smoke Detection (ASD) Pipe is used in sprinkler systems to transport air samples from smoke detectors to a central control panel. ASD Pipe is manufactured and distributed to follow strict specifications in accordance with NFPA 72, chapter 17, ensuring accurate and dependable smoke detection. The pipe is available from Viking SupplyNet in lengths of 10 and 15 feet.


The pipe reads "Smoke detector sampling tube" so that it can be distinguished from other CPVC pipe. These clear markings indicate its use for easy installation and maintenance! Viking's ASD CPVC Sample Pipe is delivered in color coded bags to easily distinguish from other CPVC pipe.



ASD Pipe Highlights

- UL Listed pre-cut sample pipe is intended for use with air sampling smoke detectors
- Delivered in white CPVC bags to easily distinguish from other CPVC pipe
- Manufactured with Viking BlazeMaster® CPVC for the highest quality and performance
- Sample pipes are clearly marked for easy inspection
- Compatible with the top ASD brands
- Follows strict compliance in accordance with NFPA 72
- Manufactured with Schedule 40 CPVC fire sprinkler pipe
- Available in lengths of 10 and 15 ft.
- Maximum ambient temperature is 200°F (93.3°C)

U.S. Branch Locations



For an up-to-date list of locations and Viking SupplyNet branch information, please visit supplynet.com/locations.