

Fig. 7 - Offset Pipe Clamp

Size Range — 1/2" thru 12" pipe

Material — Carbon Steel


Function — Recommended for support of pipe lines running at a definite distance from the wall or floor of a building or structure.

Maximum Temperature — 650°F

Finish — Plain

Note — Available in Electro-Galvanized and HDG finish or Stainless Steel materials. Special "B" dimensions available on request, consult factory.

Order By — Figure number, pipe size and finish



Dimensions • Weights

Pipe Size	A	B	Hole Size C	Bolt Size	Max. Rec. Load Lbs.	Approx. Wt./100
1/2	5 ¹³ / ₁₆	2 ⁷ / ₁₆	7/16	3/8	190	107
3/4	5 ¹⁵ / ₁₆	2 ¹ / ₂	7/16	3/8	190	109
1	6 ¹ / ₄	2 ⁵ / ₈	7/16	3/8	190	116
1 ¹ / ₄	6 ¹¹ / ₁₆	2 ³ / ₄	7/16	3/8	190	126
1 ¹ / ₂	6 ¹⁵ / ₁₆	3	7/16	3/8	190	134
2	8 ⁵ / ₁₆	3 ³ / ₁₆	7/16	3/8	420	191
2 ¹ / ₂	8 ⁷ / ₈	3 ⁷ / ₁₆	7/16	3/8	420	209
3	9 ¹ / ₂	3 ³ / ₄	7/16	3/8	420	232
3 ¹ / ₂	10 ¹ / ₁₆	4	7/16	3/8	420	250
4	10 ⁹ / ₁₆	4 ¹ / ₄	9/16	1/2	610	370
6	14 ³ / ₈	5 ⁵ / ₁₆	9/16	1/2	870	650
8	16 ⁷ / ₁₆	6 ⁵ / ₁₆	9/16	1/2	870	787
10	21 ¹ / ₂	7 ³ / ₈	13/16	3/4	925	1238
12	24 ⁷ / ₈	8 ³ / ₈	13/16	3/4	1225	2100

Fig. 8 - Extended Pipe Clamp

Size Range — 3/4" thru 8" pipe

Material — Carbon Steel

Function — For suspending or supporting piping runs where the pipe cannot be determined until installation. Field modify to suit conditions

Maximum Temperature — 650°F

Finish — Plain

Note — Available in Electro-Galvanized and HDG finish or Stainless Steel materials. Special "B" dimensions available on request, consult factory.

Order By — Figure number, pipe size and finish

Dimensions • Weights				
Pipe Size	A	B	Bolt Size	Approx. Wt./100
3/4	4 ⁷ / ₁₆	12	3/8	225
1	4 ¹¹ / ₁₆	12	3/8	230
1 ¹ / ₄	5	12	3/8	235
1 ¹ / ₂	5 ¹ / ₄	12	3/8	240
2	6	12	1/2	345
2 ¹ / ₂	7 ¹ / ₄	12	1/2	360
3	7 ⁷ / ₈	12	1/2	375
3 ¹ / ₂	8 ³ / ₈	12	12	390
4	9 ¹ / ₄	12	1/2	500
5	10 ¹ / ₂	12	1/2	545
6	12 ¹ / ₂	12	5/8	870
8	14 ⁵ / ₈	12	5/8	980

