



TECHNICAL DATA

VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
 Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
 Visit the Viking website for the latest edition of this technical data page.

1. GENERAL DESCRIPTION

The bladder tank is a carbon steel pressure vessel containing an elastomeric bladder between the water and foam concentrate. The bladder permits water pressure to be transferred to the foam concentrate without the two fluids mixing together.

This document is intended for trained experts. It contains basic information needed to use the product described. Legally binding is the product operation and maintenance manual, which must be observed.

For more information, please contact the appropriate sales office in Section 5 Availability or refer to the technical documentation. The contents of this publication are subject to modifications without notice.

2. LISTINGS AND APPROVALS

The bladder tank is FM Approved and/or UL Listed as part of a fire extinguishing system combining designated foam concentrates, specific proportioning equipment, and discharge devices. Approved and Listed system components can be found at www.approvalguide.com and <https://iq.ulprospector.com>



FM Approved – Low-Expansion Foam Systems (FM5130)



UL Listed – Guide GFGV.EX27255 & GHXV.EX5002 (UL162)

Constructed according to ASME Boiler and Pressure Vessel Code (BPVC) Sec.VIII Div.1 with U-1A ("U" Stamp certification process.



CNBOP Approved CNBOP-PIB-KOT-2024/0411-1005
 wydanie 1 F001/01/0924 CNBOP-PIB



CE marked according to the PED Directive 2014/68/EU (Europe only)

NOTE: Other international approval certificates may be available upon request.

"SFFF compatible" refers to this product as being part of a SFFF Foam system that has been tested to recognized standards. Not all configurations are available. Consult technical data and/or the Approval/Listing for usage requirements.



Photographs are for illustration purposes only. Refer to drawings for actual design details.



WARNING: Cancer and Reproductive Harm-
www.P65Warnings.ca.gov



TECHNICAL DATA

VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Visit the Viking website for the latest edition of this technical data page.

3. TECHNICAL DATA

3.1 Construction Features

- Vertical tanks on legs, or horizontal tanks on saddles
- Legs and saddles are provided with mounting brackets/holes.
- Approved system design pressure of 175 PSI (12.1 bar) or 232 PSI (16.0 bar)
- 100% pressure-tested according to the applied design code
- Shell and heads in ASME SA-516 Gr.70
- Lockable corrosion-resistant brass tank trim/service ball valves (FM Approved or UL Listed)
- Inspection flange available on left (standard) or right side of horizontal tanks
- Machine-welded circumferential and longitudinal seams for maximum quality and durability
- Welded lifting lugs to facilitate safe handling operations
- Earth lug for electrical safety
- Safety thermal valve for water side of bladder to prevent slow over-pressure and relieve thermal fluctuations
- Bladder equipped with cast rubber caps to ensure water and foam integrity under constant pressure
- Bladder specifically tested for compatibility with foams shown in FM Approval and UL Listing
- Over-sized to permit concentrate thermal expansion (volume expansion allowance)
- Tank equipped with inside protection at any opening to ensure no damage to the bladder
- Internal PVC foam concentrate distribution pipe ensures optimal foam concentrate usage
- Internal water distribution channel to equalize the water pressure everywhere avoiding damage to the bladder and to drain the tank during service and maintenance
- Nameplate holder to avoid undetected corrosion on the tank's shell behind the plate
- Sight tube level indicator
- External epoxy zinc rich primer with aliphatic polyurethane finish tested by FM and UL for corrosive atmosphere (salt fog)

3.2 Standard Materials

Table 3.2.1 - Standard Materials

Tank shell and heads:	ASME SA-516 Gr. 70
Bladder:	Reinforced NBR and EPDM
Trim valves:	Brass
Safety thermal relief valve:	Brass
Level indicator:	Sight tube: PVC
Paint:	Epoxy zinc rich primer with aliphatic polyurethane finish
Standard colour:	Flame red RAL3000
Connection:	Grooved (2.5" available with 73.0 or 76.1 mm - specify upon ordering)

3.3 Standard Design Specifications

Table 3.3.1 - Standard Design Specifications

Design pressure:	175 PSI / 12.1 bar (1.2MPa) or 232 PSI /16.0 bar (1.6MPa)
Operating temperature range*:	35°F to 120°F (1.7°C to 49°C)
Capacity:	See tables
Empty weight:	See tables
Proportioning range:	See ratio controller datasheet

(*) Refer to the appropriate proportioner for foam concentrate being used.



TECHNICAL DATA

VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Visit the Viking website for the latest edition of this technical data page.

3.4 Ordering Information

The following information is provided to ensure that the correct design requirements are provided during the order and manufacturing process. Mandatory information is required in every case. Optional information is required in case of special project or specification requirements.

Table 3.4.1: Ordering Information			
	Ref	Criteria	Option
Mandatory Information (required for quote/order processing)	1a	Configuration	a) Vertical b) Horizontal
	1b	Capacity	a) 25 to 3,400 US gallons vertical b) 50 to 3,400 US gallons horizontal (See tables for available sizes)
	1c	Design Code	ASME Bolier and Pressure Vessel (BPVC) code with U-1A manufacturer data report
	1d	Standby Pressure Rating	a) 175 PSI / 12.1 bar (1.2 MPa) b) 232 PSI /16.0 bar (1.6 MPa)
	1e	Inspection Flange	a) Left (Standard) b) Right (Required for Horizontal Tanks only)
	1g	Language	Select Bladder Tank Manual Language (see Table 12.1.2)
Optional	2a	Design Temperature	Contact technical department
	2b	Corrosion Allowance	Contact technical department
	2c	Radiographic Test Report (*)	Contact technical department
	2d	Liquid Penetrant Test Report (*)	Contact technical department
Pre-Assembled with Ratio Controller	3a	Ratio Controller Size(s)	2", 2.5", 3", 4", 6", 8"
	3b	Direction of Flow	a) Left to right b) Right to left (Direction of flow as you face the tank)
	3c	Water Line Piping	Carbon steel
	3d	Foam Line Piping	a) Brass b) Stainless steel
	3e**	Foam Concentrate Type(**)	a) Fomtec Fomtec LS xMax 3% b) Fomtec Enviro ARK 3% c) Fomtec Enviro USP 3%
	3f	Concentrate Control Valve	Viking halar CCV (FM or UL) or hydraulic ball valve
(*) With additional cost			
(**) These foam concentrates have been tested for bladder compatibility, as per FM5130 and/or UL162. The long term compatibility of other foams concentrates cannot be verified.			

INFORMATION

Some of the available options may be not covered by the FM Approval or UL Listing. Always make reference to the appropriate approval directory or guides or contact the appropriate sales office in Section 5 Availability for more assistance.



TECHNICAL DATA

VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Visit the Viking website for the latest edition of this technical data page.

4. SCOPE OF DELIVERY

Ensure that all components are complete and in good condition.

The bladder tank is supplied in or on a suitable wooden pallet skid or shipping crate in the horizontal position.

All bladder tanks have lifting lugs to allow safe maneuverability on site.

Tank is supplied empty with pre-installed bladder.

Small trim valves and contents level device are supplied pre-assembled to the tank as standard.

Safety thermal relief valve supplied as standard, unmounted from tank. UV-marked safety valve, according to ASME BPVC Sec. VIII Div.1 available for an additional cost.

Anchor fixing bolts are not part of our supply scope.

Table 4.1.1 - Documentation

Standard Documentation	Optional Documentation *
Warranty Certificate	Dimensional Drawings
PED Declaration or Conformity	Material Certificates according to ASME Code Specifications
Safety Thermal Relief Valve Declaration of Conformity	Certificate of Conformity Type 2.1 to EN10204
Hydrostatic Pressure Test Certificate	Design Structural Calculations
Bladder Pneumatic Test Certificate	Spot or Full Radiographic Examination with Report (when not mandatorily required by design parameters)
Painting Inspection Certificate	Spare Parts List
Final Inspection Certificate	Copy of Procedure Qualification Record (PQR) and Welding Procedure Specification (WPS) according to tank construction code
Operating, Filling and Maintenance Manual (English)	Operating, Filling and Maintenance Manual (Language)
Manufacturer Data Report Form U-1A	

(*) Contact the sales office listed in section 5 for further information and price.

5. AVAILABILITY

The product is available directly from Viking and from official distributors only.

Americas:

The Viking Corporation

5150 Beltway SE

Caledonia, MI 49316

Tel.: (800) 968-9501

Fax: 269-818-1680

Technical Services: 1-877-384-5464

techsvcs@vikingcorp.com

6. PRODUCT VARIANTS

6.1 Options

- Flanged connections (ANSI or PN16)
- Special coatings for salt-water applications or harsh environmental conditions
- Nameplate in corrosion-resistant material
- Increased wall thickness for corrosion allowance
- Internal coatings, such as epoxy tar
- 232 PSI /16.0 bar (1.6 MPa) design pressure rating with FM Approval and UL Listing
- Other design pressure and seismic ratings
- Ladders, work platform, sunshield
- Full bladder tank stainless steel construction
- Heat tracing and/or insulation
- Bladder tank pre-installed on base frame or containerized to customer requirements
- Various colors and painting cycles with FM Approval and UL Listing (120-300 microns)
- Non-destructive examinations
- Factory acceptance test, notified body, or third-party inspections
- Special sea freight and fumigated packaging
- UV-certified safety valve according to ASME BPVC Code Sec.VIII Div.1

Contact us for more details, pricing, and availability.

INFORMATION

Some of the available options may be not covered by the FM Approval or UL Listing. Always make reference to the appropriate approval directory or guides or contact us for more assistance.



TECHNICAL DATA

VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Visit the Viking website for the latest edition of this technical data page.

6.2 General bladder tank layout and P&ID




Figure 6.2.1
Vertical and Horizontal Bladder Tanks

Table 6.2.2 - General Bladder Tank Layout and P&ID

Item	Description	Item	Description
1	Bladder tank	7	Water filling/drain valve (NPT)
2	Water vent valve (NPT)	8	Foam concentrate filling/drain valve (NPT)
3	Safety thermal relief valve	9	Concentrate level indicator drain valve
4	Foam concentrate vent valve (NPT)	10	Concentrate level indicator
5	Filling vent valve (Optional)	11	Water shut-off valve (to be ordered separately)
6	Filling pressure gauge 1-10 kpa (Optional)	12	Foam concentrate shut-off valve (to be ordered separately)

Note: Item 10 shown with sight tube. Level gauge also available and connected at position 10.




Figure 6.2.3



TECHNICAL DATA



VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Visit the Viking website for the latest edition of this technical data page.

6.3 Dimensions





TECHNICAL DATA

VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
 Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
 Visit the Viking website for the latest edition of this technical data page.

Table 6.3.3 - Vertical Bladder Tank Dimensions (ASME Sec VIII Design Code)

ASME Sec VIII Design Code		Capacity		Weight		A	B	C	ØD	E	ØF	ØG	H	ØL	M	N
175 PSI / 12.1 bar	232 PSI / 16.0 bar	USG	Litres	LBS	KG	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm
VFTV0025U	VFTV0025U-16	25	94	221	100	6.4 163	15.7 400	7.0 178	19.7 500	30.2 768	22.4 570	2 50	48.1 1221	2 50	9.8 250	0.6 15
VFTV0036U	VFTV0036U-16	36	136	309	140	6.4 163	23.6 600	7.0 178	19.7 500	38.1 968	22.4 570	2 50	55.9 1421	2 50	9.8 250	0.6 15
VFTV0050U	VFTV0050U-16	50	189	411	186	7.4 187	27.6 700	8.0 203	23.6 600	44.5 1130	26.4 670	2 50	61.8 1570	2 50	9.8 250	0.6 15
VFTV0075U	VFTV0075U-16	75	283	450	204	7.4 187	35.4 900	8.0 203	23.6 600	44.5 1130	26.4 670	2 50	69.7 1770	2 50	9.8 250	0.6 15
VFTV0100U	VFTV0100U-16	100	378	528	239	7.4 187	49.2 1250	8.0 203	23.6 600	64.6 1640	26.4 670	2 50	83.4 2120	2 50	9.8 250	0.59 15
VFTV0150U	VFTV0150U-16	150	567	850	385	10.3 262	39.4 1000	10.8 274	31.5 800	57.1 1450	34.3 870	2 50	79.4 2016	2 50	9.8 510	0.6 15
VFTV0200U	VFTV0200U-16	200	757	938	425	10.3 262	51.2 1300	10.8 274	31.5 800	57.1 1450	34.3 870	2 50	91.2 2316	2 50	9.8 510	0.6 15
VFTV0250U	VFTV0250U-16	250	946	940	426	12.9 327	39.4 1000	13.2 336	39.4 1000	59.7 1516	42.6 1082	2.5 65	84.3 2142	2.5 65	24.0 610	0.6 15
VFTV0300U	VFTV0300U-16	300	1135	1091	494	12.9 327	51.2 1300	13.2 336	39.4 1000	71.5 1816	42.6 1082	2.5 65	96.1 2442	2.5 65	24.0 610	0.6 15
VFTV0350U	VFTV0350U-16	350	1324	1113	504	12.9 327	55.1 1400	13.2 336	39.4 1000	75.4 1916	42.6 1082	2.5 65	100.1 2542	2.5 65	24.0 610	0.6 15
VFTV0400U	VFTV0400U-16	400	1514	1150	521	12.9 327	65.0 1650	13.2 336	39.4 1000	85.3 2166	42.6 1082	2.5 65	109.9 2792	2.5 65	24.0 610	0.6 15
VFTV0450U	VFTV0450U-16	450	1703	1823	826	13.0 329	59.1 1500	13.3 337	43.3 1100	79.4 2017	46.5 1181	2.5 65	104.1 2645	2.5 65	24.0 610	0.6 15
VFTV0500U	VFTV0500U-16	500	1892	2004	908	13.0 329	70.9 1800	13.3 337	43.3 1100	91.2 2317	46.5 1181	2.5 65	115.9 2945	2.5 65	24.0 610	0.6 15
VFTV0600U	VFTV0600U-16	600	2271	2267	1027	13.0 330	65.0 1650	14.5 368	47.2 1200	84.6 2148	51.2 1300	3 80	110.5 2807	3 80	37.4 950	0.6 15
VFTV0700U	VFTV0700U-16	700	2649	2514	1139	14.1 358	65.0 1650	15.5 394	51.2 1300	86.4 2194	55.3 1405	3 80	113.4 2881	3 80	33.5 850	0.6 15
VFTV0800U	VFTV0800U-16	800	3028	2695	1221	14.1 358	78.7 2000	15.5 394	51.2 1300	100.2 2544	55.3 1405	3 80	127.2 3231	3 80	33.5 850	0.6 15
VFTV0900U	VFTV0900U-16	900	3406	2928	1328	15.3 388	78.7 2000	16.5 420	55.1 1400	100.0 2540	59.3 1505	3 80	129.4 3287	3 80	36.6 930	0.6 15
VFTV1000U	VFTV1000U-16	1000	3785	3583	1623	15.8 402	82.7 1900	17.1 434	57.1 1450	104.5 2454	61.2 1555	3 80	134.4 3215	3 80	36.6 930	0.6 15
VFTV1100U	VFTV1100U-16	1100	4163	3764	1705	15.8 402	82.7 2100	17.1 447	57.1 1500	104.5 2667	61.2 1605	3 80	134.4 3442	3 80	36.6 950	0.6 15
VFTV1200U	VFTV1200U-16	1200	4542	3817	1729	16.4 416	82.7 2100	17.6 447	59.1 1500	105.0 2667	63.2 1605	3 80	135.5 3442	3 80	37.4 950	0.6 15
VFTV1300U	VFTV1300U-16	1300	4921	4276	1937	17.4 443	78.7 2200	18.5 471	63.0 1600	102.0 2841	67.1 1705	3 80	133.6 3643	3 80	41.3 1050	0.6 15
VFTV1400U	VFTV1400U-16	1400	5299	4358	1974	17.4 443	88.6 2250	18.5 471	63.0 1600	111.9 2841	67.1 1705	3 80	143.4 3643	3 80	41.3 1050	0.6 15
VFTV1500U	VFTV1500U-16	1500	5678	4525	2050	19.6 497	74.8 1900	20.6 522	68.9 1750	100.1 2542	73.2 1860	3 80	133.8 3398	3 80	45.3 1150	0.6 15
VFTV1600U	VFTV1600U-16	1600	6056	4636	2100	19.6 497	78.7 2000	20.6 522	68.9 1750	104.0 2642	73.2 1860	3 80	137.7 3498	3 80	45.3 1150	0.6 15
VFTV1700U	VFTV1700U-16	1700	6435	4724	2140	20.5 521	78.7 2000	21.5 547	70.9 1800	103.4 2627	75.2 1910	3 80	139.6 3547	3 80	45.3 1150	0.6 15
VFTV1800U	VFTV1800U-16	1800	6813	5347	2422	22.6 575	59.1 1500	23.5 598	78.7 2000	88.5 2248	83.5 2120	3 80	121.3 3082	3 80	51.2 1300	0.8 20
VFTV1900U	VFTV1900U-16	1900	7192	5501	2492	22.6 575	63.0 1600	23.5 598	78.7 2000	92.4 2348	83.5 2120	3 80	125.3 3182	3 80	51.2 1300	0.8 20
VFTV2000U	VFTV2000U-16	2000	7570	5722	2592	22.6 575	68.9 1750	23.5 598	78.7 2000	98.3 2498	83.5 2120	3 80	131.2 3332	3 80	51.2 1300	0.8 20
VFTV2200U	VFTV2200U-16	2200	8327	6459	2926	22.6 575	82.7 2100	23.5 598	78.7 2000	112.1 2848	83.5 2120	3 80	145.0 3682	3 80	51.2 1300	0.8 20
VFTV2400U	VFTV2400U-16	2400	9084	6691	3031	22.6 575	88.6 2250	23.5 598	78.7 2000	119.2 3028	83.5 2120	3 80	150.9 3832	3 80	51.2 1300	0.8 20
VFTV2600U	VFTV2600U-16	2600	9842	6954	3150	22.6 575	102.4 2600	23.5 598	78.7 2000	131.8 3348	83.5 2120	3 80	164.6 4182	3 80	51.2 1300	0.8 20
VFTV2800U	VFTV2800U-16	2800	10599	7605	3445	22.6 575	114.2 2900	23.5 598	78.7 2000	143.6 3648	83.5 2120	3 80	176.5 4482	3 80	51.2 1300	0.8 20
VFTV3000U	VFTV3000U-16	3000	11356	7901	3579	22.6 575	122.0 3100	23.5 598	78.7 2000	151.5 3848	83.5 2120	3 80	184.3 4682	3 80	51.2 1300	0.8 20
VFTV3200U	VFTV3200U-16	3200	12113	8442	3824	22.6 575	133.9 3400	23.5 598	78.7 2000	163.3 4148	83.5 2120	3 80	196.1 4982	3 80	51.2 1300	0.8 20
VFTV3400U	VFTV3400U-16	3400	12870	8881	4023	22.6 575	145.7 3700	23.5 598	78.7 2000	175.1 4448	83.5 2120	3 80	208.0 5282	3 80	51.2 1300	0.8 20



TECHNICAL DATA

**VERTICAL AND HORIZONTAL
BLADDER TANKS MODEL VFT
ASME Sec.VIII Div.1 - U-1A**

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
Visit the Viking website for the latest edition of this technical data page.




Figure 6.3.4
Horizontal Bladder Tank: 50 to 100 US Gallons




Figure 6.3.5
Horizontal Bladder Tank: 150 to 3,400 US gallons



TECHNICAL DATA

VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
 Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
 Visit the Viking website for the latest edition of this technical data page.

Table 6.3.6 - Horizontal Bladder Tank Dimensions (ASME Sec VIII Design Code)

Bladder Tank : ASME Sec VIII Design Code		Capacity		Weight		A	B	C	ØD	ØG	H	ØL	M	N	O	P	Q	R
175 PSI / 12.1 bar	232 PSI / 16.0 bar	USG	Litres	LBS	KG	inch	inch	inch	inch	inch	inch	inch	inch	inch	inch	inch	inch	inch
						mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm
VFTH0050U	VFTH0050U-16	50	189	574	260	8.0	39.4	8.0	19.7	2	55.4	2	32.3	0.3	2.4	16.7	13.8	32.3
						203	1000	203	500	50	1406	50	820	8	60	425	350	820
VFTH0075U	VFTH0075U-16	75	283	640	290	9.0	39.4	9.0	23.6	2	57.3	2	32.3	0.3	2.4	19.7	16.9	32.3
						228	1000	228	600	50	1456	50	820	8	60	500	430	820
VFTH0100U	VFTH0100U-16	100	378	684	310	9.0	49.2	9.0	23.6	2	67.2	2	42.1	0.3	2.4	19.7	16.9	40.2
						228	1250	228	600	50	1706	50	1070	8	60	500	430	1020
VFTH0150U	VFTH0150U-16	150	567	828	375	10.3	39.4	10.8	31.5	2	60.5	2	51.0	0.3	4.7	19.7	15.7	32.3
						262	1000	274	800	50	1536	50	1295	8	120	500	400	820
VFTH0200U	VFTH0200U-16	200	757	883	400	10.3	51.2	10.8	31.5	2	72.3	2	62.8	0.3	4.7	19.7	15.7	42.1
						262	1300	274	800	50	1836	50	1595	8	120	500	400	1070
VFTH0250U	VFTH0250U-16	250	946	1258	570	11.3	39.4	13.2	39.4	2.5	63.9	2.5	51.0	0.3	4.7	27.6	23.6	32.3
						288	1000	336	1000	65	1624	65	1295	8	120	700	600	820
VFTH0300U	VFTH0300U-16	300	1135	1391	630	11.3	51.2	13.2	39.4	2.5	75.7	2.5	39.4	0.3	4.7	27.6	23.6	42.1
						288	1300	336	1000	65	1924	65	1000	8	120	700	600	1070
VFTH0350U	VFTH0350U-16	350	1324	1453	650	11.3	55.1	13.2	39.4	2.5	79.7	2.5	39.4	0.3	4.7	27.6	23.6	42.1
						288	1400	336	1000	65	2024	65	1000	8	120	700	600	1070
VFTH0400U	VFTH0400U-16	400	1514	1479	670	11.3	65.0	13.2	39.4	2.5	89.5	2.5	51.2	0.3	4.7	27.6	23.6	53.5
						288	1650	336	1000	65	2274	65	1300	8	120	700	600	1360
VFTH0450U	VFTH0450U-16	450	1703	2137	968	11.6	59.1	13.2	43.3	2.5	83.9	2.5	45.3	0.3	4.7	31.5	27.6	48.0
						294	1500	336	1100	65	2130	65	1150	8	120	800	700	1220
VFTH0500U	VFTH0500U-16	500	1892	2318	1050	11.6	70.9	13.2	43.3	2.5	95.7	2.5	57.1	0.3	4.7	31.5	27.6	59.8
						294	1800	336	1100	65	2430	65	1450	8	120	800	700	1520
VFTH0600U	VFTH0600U-16	600	2271	2377	1077	12.7	65.0	14.2	47.2	3	91.9	3	53.5	0.3	5.9	35.4	31.5	56.7
						322	1650	361	1200	80	2333	80	1360	8	150	900	800	1440
VFTH0700U	VFTH0700U-16	700	2649	2651	1201	13.8	65.0	15.2	51.2	3	94.0	3	58.3	0.3	5.9	35.4	31.5	56.7
						351	1650	386	1300	80	2387	80	1480	8	150	900	800	1440
VFTH0800U	VFTH0800U-16	800	3028	2898	1313	13.8	78.7	15.2	51.2	3	107.8	3	63.0	0.3	5.9	35.4	31.5	66.1
						351	2000	386	1300	80	2737	80	1600	8	150	900	800	1680
VFTH0900U	VFTH0900U-16	900	3406	3680	1667	15.3	78.7	16.3	55.1	3	110.3	3	63.0	0.3	5.9	39.4	33.5	66.1
						389	2000	413	1400	80	2801	80	1600	8	150	1000	850	1680
VFTH1000U	VFTH1000U-16	1000	3785	3592	1627	15.8	74.8	16.8	57.1	3	107.4	3	63.0	0.4	5.9	39.4	33.5	62.2
						402	1900	426	1450	80	2728	80	1600	10	150	1000	850	1580
VFTH1100U	VFTH1100U-16	1100	4163	3777	1711	15.8	82.7	16.8	57.1	3	115.3	3	63.0	0.4	5.9	39.4	33.5	66.1
						402	2100	426	1450	80	2928	80	1600	10	150	1000	850	1680
VFTH1200U	VFTH1200U-16	1200	4542	4159	1884	16.5	82.7	17.3	59.1	3	116.4	3	66.9	0.4	5.9	39.4	33.5	70.1
						418	2100	439	1500	80	2957	80	1700	10	150	1000	850	1780
VFTH1300U	VFTH1300U-16	1300	4921	4355	1973	17.5	78.7	18.3	63.0	3	114.6	3	63.0	0.4	7.9	43.3	37.4	68.1
						445	2000	465	1600	80	2910	80	1600	10	200	1100	950	1730
VFTH1400U	VFTH1400U-16	1400	5299	4629	2097	17.5	88.6	18.3	63.0	3	124.4	3	70.9	0.4	7.9	43.3	37.4	76.0
						445	2250	465	1600	80	3160	80	1800	10	200	1100	950	1930
VFTH1500U	VFTH1500U-16	1500	5678	4525	2050	19.6	74.8	20.6	68.9	3	115.0	3	61.0	0.4	7.9	47.2	41.3	63.4
						498	1900	522	1750	80	2920	80	1550	10	200	1200	1050	1610
VFTH1600U	VFTH1600U-16	1600	6056	4746	2150	19.6	78.7	20.6	68.9	3	118.9	3	61.0	0.4	7.9	47.2	41.3	65.4
						498	2000	522	1750	80	3020	80	1550	10	200	1200	1050	1660
VFTH1700U	VFTH1700U-16	1700	6435	4967	2250	20.2	78.7	21.1	70.9	3	120.0	3	61.0	0.4	7.9	47.2	41.3	66.1
						513	2000	535	1800	80	3047	80	1550	10	200	1200	1050	1680
VFTH1800U	VFTH1800U-16	1800	6813	5700	2582	22.3	59.1	23.1	78.7	3	104.4	3	47.2	0.4	9.8	59.1	53.1	49.2
						566	1500	586	2000	80	2652	80	1200	10	250	1500	1350	1250
VFTH1900U	VFTH1900U-16	1900	7192	5854	2652	22.3	63.0	23.1	78.7	3	108.3	3	52.4	0.4	9.8	59.1	53.1	49.2
						566	1600	586	2000	80	2752	80	1330	10	250	1500	1350	1250
VFTH2000U	VFTH2000U-16	2000	7570	6086	2757	22.3	68.9	23.1	78.7	3	114.3	3	52.4	0.4	9.8	59.1	53.1	55.1
						566	1750	586	2000	80	2902	80	1330	10	250	1500	1350	1400
VFTH2200U	VFTH2200U-16	2200	8327	6581	2981	22.3	82.7	23.1	78.7	3	128.0	3	63.0	0.4	9.8	59.1	53.1	68.9
						566	2100	586	2000	80	3252	80	1600	10	250	1500	1350	1750
VFTH2400U	VFTH2400U-16	2400	9084	6823	3091	22.3	88.6	23.1	78.7	3	133.9	3	68.9	0.4	9.8	59.1	53.1	74.8
						566	2250	586	2000	80	3402	80	1750	10	250	1500	1350	1900
VFTH2600U	VFTH2600U-16	2600	9842	7362	3335	22.3	102.4	23.1	78.7	3	147.7	3	82.7	0.4	9.8	59.1	53.1	88.6
						566	2600	586	2000	80	3752	80	2100	10	250	1500	1350	2250
VFTH2800U	VFTH2800U-16	2800	10599	7870	3565	22.3	114.2	23.1	78.7	3	159.5	3	94.5	0.4	9.8	59.1	53.1	100.4
						566	2900	586	2000	80	4052	80	2400	10	250	1500	1350	2550



TECHNICAL DATA

VERTICAL AND HORIZONTAL BLADDER TANKS MODEL VFT ASME Sec.VIII Div.1 - U-1A

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Visit the Viking website for the latest edition of this technical data page.

Table 6.3.6 - Horizontal Bladder Tank Dimensions (ASME Sec VIII Design Code) (cont.)

Bladder Tank : ASME Sec VIII Design Code		Capacity		Weight		A	B	C	ØD	ØG	H	ØL	M	N	O	P	Q	R
175 PSI / 12.1 bar	232 PSI / 16.0 bar	USG	Litres	LBS	KG	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm	inch mm
VFTH3000U	VFTH3000U-16	3000	11356	8177	3704	22.3	122.0	23.1	78.7	3	167.4	3	102.4	0.4	9.8	59.1	53.1	108.3
						566	3100	586	2000	80	4252	80	2600	10	250	1500	1350	2750
VFTH3200U	VFTH3200U-16	3200	12113	8618	3904	22.3	133.9	23.1	78.7	3	179.2	3	114.2	0.4	9.8	59.1	53.1	120.1
						566	3400	586	2000	80	4552	80	2900	10	250	1500	1350	3050
VFTH3400U	VFTH3400U-16	3400	12870	8925	4043	22.3	141.7	23.1	78.7	3	187.1	3	126.0	0.4	9.8	59.1	53.1	131.9
						566	3600	586	2000	80	4752	80	3200	10	250	1500	1350	3350

7. INSTALLATION

Refer to appropriate Installation Standards (i.e., NFPA, VdS, LPCB, etc.) and/or FM applicable FM Global Property Loss Prevention datasheets, such as 4-12, Foam-Water Sprinkler Systems. The Installation, Operation, and Maintenance Bladder Tank manual shall also be referenced.

NOTICE

When designing a bladder tank into your fire protection system, give consideration to future maintenance activities. Ensure that adequate clearance above a vertical bladder tank or at the inspection flange end of a horizontal tank is allowed. For more guidance, contact us.

8. OPERATION

1. Foam concentrate is stored inside the bladder. When used in conjunction with a ratio controller, it proportions foam concentrate accurately into the water stream.
2. During system activation, the outer side of the bladder is pressurized by the system water supply, which forces foam concentrate to the proportioner or a ratio controller.
3. Simultaneously, as water flows through the venturi area of the wide-range proportioner or ratio controller, a metered pressure drop draws foam concentrate into the system water stream, creating a foam solution mixed to the appropriate ratios.
4. The foam solution flows through the system pipework and out of any open sprinklers, nozzles, or other discharge devices.
5. As the foam concentrate continues to flow from the inside of the bladder, system water enters the bladder tank on the outside of the bladder, keeping a balanced pressure system.

9. GUARANTEE

For warranty details, refer to Viking's current list price schedule or contact Viking directly.



TECHNICAL DATA

**VERTICAL AND HORIZONTAL
BLADDER TANKS MODEL VFT
ASME Sec.VIII Div.1 - U-1A**

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
Visit the Viking website for the latest edition of this technical data page.

10. INSPECTION, TESTS AND MAINTENANCE

⚠ WARNING

Any system maintenance or testing that involves placing a control valve or detection system out of service may eliminate the fire protection capabilities of that system. Prior to proceeding, notify all Authorities Having Jurisdiction. Consideration should be given to employment of a fire patrol in the affected area.

Refer to respective requirements, according to the relevant standards for inspection, testing, and maintenance. If applicable, refer to FM Global Property Loss Prevention datasheet 4-12 for specific test and commissioning criteria. Additionally, the Authority Having Jurisdiction (AHJ) may require more maintenance, testing, and inspection standards to be followed.

11. DISPOSAL

At end of use the product described here should be disposed of via the national recycling system. Upon request the manufacturer can take back and properly dispose of the electrical equipment and electronic devices.

12. ACCESSORIES AND SPARE PARTS

Contact the appropriate sales office in Section 5 Availability for assistance.

13. DECLARATION OF CONFORMITY

If required, contact the appropriate sales office in **Section 5 Availability** for more assistance.

Table 12.1.1 - Optional / Standard Spare Parts

Description	Material	Connection	Part Number	
			175 PSI (12 bar) Tanks	16 bar Tanks
Safety thermal relief valve	Brass	1/2"	B10C12.1	B10C16
ASME safety valve	Carbon steel	3/4"	EUV34CS-12.1	EUV34CS-16.0
ASME safety valve	Stainless steel 316	3/4"	EUV34SS-12.1	EUV34SS-16.0
Filling device & KPA gauge	Carbon steel	1"	FILLDEVICE	
Replacement bladder	Various	Contact us with tank serial number		
Sight tube replacement kit	Various	Contact us with tank serial number		

Table 12.1.2 - Bladder Tank Manual

Language	Part Number	Language	Part Number
English	F032216-EN	Dutch	F032216-NL
German	F032216-DE	Polish	F032216-PL
Spanish	F032216-ES	Swedish	F032216-SV
French	F032216-FR	Turkish	F032216-TR
Italian	F032216-IT	--	--