

Pressure Gauges

Gauges for sprinkler systems and fire pumps are designed for use with air or water. These gauges are usually of the Bourdon tube type. The moving parts are fabricated of appropriate corrosion-resistant materials.

When installed on the air side of a dry pipe system, a retard type gauge may be used. This gauge is assembled with a tube appropriate to the unretarded pressure range of the gauge and is provided with a spring to resist the full scale load.

The two common sizes are 4 1/2 and 3 1/2 in. diameter. These gauges can be calibrated with a hydraulic testing unit by adjusting the dial pointer to read correctly at known pressures. Accuracy requirements are that the gauge be correct within 2% over the center third of its scale and within 3% over the remaining two-thirds. Dial marking subdivisions correspond to the maximum accuracy of the gauge.

For service on fire pumps where the suction may be taken under a lift, compound pressure vacuum gauges are available graduated in pressure units over both the pressure and vacuum scales, and are designed not to be injured by vacuum.

To minimize possible damage and provide maximum accuracy, gauges should be selected with scales of about twice the maximum system pressure.

Type 35-W1005P-02L-XUL

"Ashcroft" Brand Type 35-W1005P-02L-XUL Pressure Gauge. 0-100 psi (0-690 kPa), 0-150 psi (0-1035 kPa), 0-250 psi (0-1725 kPa), 0-300 psi (0-2070 kPa), 0-600 psi (0-4135 kPa). 3 1/2 in. Retard Pressure Gauge. 0-80-250 psi (0-550-1725 kPa).

Company Name:	Ashcroft Inc
Company Address:	250 E Main St, Stratford, Connecticut 06614, USA
Company Website:	http://www.ashcroftinc.com
Listing Country:	United States of America
Certification Type:	FM Approved

Pressure Gauges

Gauges for sprinkler systems and fire pumps are designed for use with air or water. These gauges are usually of the Bourdon tube type. The moving parts are fabricated of appropriate corrosion-resistant materials.

When installed on the air side of a dry pipe system, a retard type gauge may be used. This gauge is assembled with a tube appropriate to the unretarded pressure range of the gauge and is provided with a spring to resist the full scale load.

The two common sizes are 4 1/2 and 3 1/2 in. diameter. These gauges can be calibrated with a hydraulic testing unit by adjusting the dial pointer to read correctly at known pressures. Accuracy requirements are that the gauge be correct within 2% over the center third of its scale and within 3% over the remaining two-thirds. Dial marking subdivisions correspond to the maximum accuracy of the gauge.

For service on fire pumps where the suction may be taken under a lift, compound pressure vacuum gauges are available graduated in pressure units over both the pressure and vacuum scales, and are designed not to be injured by vacuum.

To minimize possible damage and provide maximum accuracy, gauges should be selected with scales of about twice the maximum system pressure.

Model 111.10SP.100

Air or Water Pressure Gauge - Model 111.10SP.100

- 0-300 psi (0-2068 kPa). 4 in. (100 mm) size, Plastic Case.
- 0-300 psi (0-2068 kPa). 4 in. (100 mm) size, Steel case with brass plated finish.
- 0-400 psi (0-2760 kPa). 4 in. (100 mm) size, Plastic Case.
- 0-400 psi (0-2760 kPa). 4 in. (100 mm) size, Steel case with brass plated finish.
- 0-600 psi (0-4140 kPa). 4 in. (100 mm) size, Plastic case.
- 0-600 psi (0-4140 kPa). 4 in. (100 mm) size, Steel case with brass plated finish.

Retard Pressure Gauge - Model 111.10SP.100

- 0-80-250 psi (0-550-1725 kPa). 4 in. (100 mm) size

These gauges have a BSP or 1/4 in. male NPT bottom connection.

Company Name:	Wika Instrument Corp
Company Address:	1000 Wiegand Blvd, Lawrenceville, Georgia 30043, USA
Company Website:	http://www.wika.com
Listing Country:	United States of America
Certification Type:	FM Approved