

	<h2 style="margin: 0;">TECHNICAL BULLETIN</h2>	<h3 style="margin: 0;">AIR ASPIRATING SMOKE DETECTOR SAMPLE TUBES</h3>
---	--	--

The Viking Corporation, 5150 Beltway Dr. SE, Caledonia, MI, 49316
 Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
 Visit the Viking website for the latest edition of this technical data page www.vikinggroupinc.com

1. DESCRIPTION

The sample tubes are pre-cut air sampling tubes intended for use with air aspirating smoke detectors. The tube is manufactured of SDR 13.5 CPVC fire sprinkler pipe and is UL Listed.

2. LISTINGS


 cULus Listed: EX.15165, Listed to UL 1821 and tested to UL 1887

3. TECHNICAL DATA

- Indoor use only
- Compound cell class: 23547
- Rated water working pressure (WWP): 64 psi (4.4 bar) at 200°F (93.3°C)
- Maximum ambient temperature: 200°F (93.3°C)



Ordering Information

Part Number	Nominal Pipe Size	Length
25676	3/4"	15'
25676-10	3/4"	10'

4. INSTALLATION

Install the sampling tube in accordance with the smoke detector manufacturer's instructions.

MARKINGS

