



TECHNICAL DATA

MICROMATIC® STANDARD RESPONSE UPRIGHT SPRINKLER VK200 (K8.0)

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Visit the Viking website for the latest edition of this technical data page: www.vikinggroupinc.com

1. DESCRIPTION

The Viking Micromatic® Standard Response Upright VK200 Sprinkler is a small, thermosensitive, glass-bulb spray sprinkler available in several different finishes, temperature ratings, and K-Factors to meet design requirements. The special Polyester and Electroless Nickel PTFE (ENT) coatings can be used in decorative applications where colors are desired. In addition, these coatings have been investigated for installation in corrosive environments and are listed/approved as indicated in the Approval Charts.

Viking standard response sprinklers may be ordered and/or used as open sprinklers (glass bulb and pip cap assembly removed) on deluge systems. Refer to Ordering Instructions.

2. LISTINGS AND APPROVALS



cULus Listed: Category VNIV



FM Approved: Class Series 2000



VdS Approved: Certificates G414013, G414014, G498006, and G4060055



LPCB Approved: Certificate 096e/06



CE Certified: Standard EN 12259-1, EC-certificate of conformity 0832-CPD-2001, EC-certificate of constancy of performance 0832-CPR-S0021

China Approval: Approved according to China GB Standard



MED Certified: Standard EN 12259-1, EC-certificate of conformity 0832-MED-1003

NOTE: Other International approval certificates are available upon request.

Refer to Approval Charts and Design Criteria for listing and approval requirements that must be followed.

3. TECHNICAL DATA

Specifications:

Minimum Operating Pressure: 7 psi (0.5 bar)†
 Maximum Working Pressure: 175 psi (12 bar) wwp
 Factory tested hydrostatic rating: 500 psi (34.5 bar)
 Thread size: 1/2" NPT, 15 mm BSP, 3/4" NPT, 20 mm BSPT
 Nominal K-Factor: 8.0 U.S. (115.2 metric**)
 Glass-bulb fluid temperature rating: -65 °F (-55 °C)
 Overall Length: 2-3/8" (60 mm)

† cULus Listing, FM Approval, and NFPA 13 installs require a minimum of 7 psi (0.5 bar). The minimum operating pressure for LPCB and CE Approvals ONLY is 5 psi (0.35 bar).

** Metric K-factor measurement shown is in Bar. When pressure is measured in kPa, divide the metric K-factor shown by 10.0.

Material Standards:

Frame Casting: Brass UNS-C84400
 Deflector: Copper UNS-C19500
 Bulb: Glass, nominal 5 mm diameter
 Belleville Spring Sealing Assembly: Nickel Alloy, coated on both sides with PTFE Tape
 Screw: Brass UNS-C36000
 Pip Cap and Insert Assembly: Copper UNS-C11000 and Stainless Steel UNS-S30400
 For Polyester Coated Sprinklers: Belleville Spring-Exposed
 For ENT coated Sprinklers: Belleville Spring - Exposed, Screw and Pipcap - ENT plated.

††Not for FM Approval.

Ordering Information: Refer to Table 1.

4. INSTALLATION

Refer to appropriate NFPA Installation Standards.

5. OPERATION

During fire conditions, the heat-sensitive liquid in the glass bulb expands, causing the glass to shatter, releasing the pip cap and sealing spring assembly. Water flowing through the sprinkler orifice strikes the sprinkler deflector, forming a uniform spray pattern to extinguish or control the fire.



WARNING: Cancer and Reproductive Harm-
www.P65Warnings.ca.gov



TECHNICAL DATA

MICROMATIC® STANDARD RESPONSE UPRIGHT SPRINKLER VK200 (K8.0)

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058

Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

Visit the Viking website for the latest edition of this technical data page: www.vikinggroupinc.com

6. INSPECTIONS, TESTS AND MAINTENANCE

Refer to NFPA 25 for Inspection, Testing and Maintenance requirements.

7. AVAILABILITY

The Viking Micromatic® Standard Response Upright Sprinkler VK200 is available through a network of domestic and international distributors. See The Viking Corporation web site for the closest distributor or contact The Viking Corporation.

8. GUARANTEE

For details of warranty, refer to Viking's current list price schedule or contact Viking directly.

TABLE 1: ORDERING INFORMATION

Instructions: Using the sprinkler base part number,
(1) add the suffix for the desired Finish
(2) add the suffix for the desired Temperature Rating.

| Sprinkler Base Part No. | Size | | 1: Finishes | | 2: Temperature Ratings | | | | |
|-------------------------------|-------------|------------|--------------------|---------------------|------------------------|---------------|--------------------------|--|--------|
| | NPT Inch | BSPT mm | Description | Suffix ¹ | Nominal Rating | Bulb Color | Hazard Classification | Max. Ambient Ceiling Temperature ² | Suffix |
| 18263 | 3/4 | -- | Brass | A | 135 °F (57 °C) | Orange | Ordinary | 100 °F (38 °C) | A |
| 18266 | -- | 20 | Chrome | F | 155 °F (68 °C) | Red | Ordinary | 100 °F (38 °C) | B |
| 18268 ⁹ | 1/2 | -- | White Polyester | M-/W | 175 °F (79 °C) | Yellow | Intermediate | 150 °F (65 °C) | D |
| 20377 ⁹ | -- | 20 | Black Polyester | M-/B | 200 °F (93 °C) | Green | Intermediate | 150 °F (65 °C) | E |
| | | | Wax | C | 286 °F (141 °C) | Blue | High | 225 °F (107 °C) | G |
| | | | Wax over Polyester | V-/W | 360 °F (182 °C) | Mauve | Extra High | 300 °F (149 °C) | H |
| | | | ENT ³ | JN | 500 °F (260 °C) | Black | Ultra High ⁶ | 465 °F (240 °C) | L |

Example: 13001MB/W = VK200 with White Polyester Finish and 155 °F (68 °C) Nominal temperature rating. This sprinkler is to be installed into an area with a maximum ambient temperature of 100 °F (38 °C) meaning if the area will experience temperatures above the maximum ambient rating, you shall use a higher temperature-rated sprinkler.

Corrosion Resistant Coatings⁵

- White Polyester and Black Polyester in all temperature ratings.
- ENT in all temperature ratings except 135 °F (57 °C).
- Wax-Coated Brass and Wax over Polyester⁷ for sprinklers with the following temperature ratings:
155 °F (68 °C) Lt. Brown Wax | 175 °F (79 °C) Brown Wax | 200 °F (93 °C) Brown Wax | 286 °F (141 °C) Dk. Brown Wax⁷

Accessories

Sprinkler Wrenches (see Figure 1):

- Standard Wrench: Part No. 21475M/B
- Standard Wrench for Wax Coated Sprinklers: Part No. 10896W/B
- Socket Wrench for Recessed Pendent Sprinklers: Part No. 13655W/B (A 1/2" ratchet is required, not available from Viking)
- Socket Wrench for Wax Coated Sprinklers: Part No. 13577W/B (A 1/2" ratchet is required, not available from Viking)
- Optional Protective Sprinkler Cap Remover/Escutcheon Installer Tool⁹: Part No. 15915

Sprinkler Cabinet:

- Up to 6 sprinklers: Part number 01724A (available since 1971).
- 6-12 Sprinklers: Part number 01725A (available since 1971).

Footnotes




- Where a dash (-) is shown in the Finish suffix designation, insert the desired Temperature Rating suffix. See example above.
- Based on NFPA 13, NFPA 13R, and NFPA 13D. Other limits may apply, depending on fire loading, sprinkler location, and other requirements of the Authority Having Jurisdiction. Refer to specific installation standards.
- FM Approved corrosion resistant.
- The corrosion resistant and corrosion proofing coatings have passed the standard corrosion test required by the approving agencies indicated in the Approval Chart(s). These tests cannot and do not represent all possible corrosive environments. Prior to installation, verify through the end-user that the coatings are compatible with or suitable for the proposed environment. For automatic sprinklers, the coatings indicated are applied to the exposed exterior surfaces only. Note that the spring is exposed on sprinklers with Polyester and ENT coatings. For ENT coated automatic sprinklers, the waterway is coated.
- Sprinklers of Ultra-High temperature rating are intended for use inside ovens, dryers, or similar enclosures with normal operating temperatures above 300 °F (149 °C). Where the ambient temperature around the Ultra-High temperature rated sprinkler is significantly reduced below 300 °F (149 °C), response time may be severely retarded.
- Wax melting point is 170 °F (76 °C) for 286 °F (141 °C) temperature rated sprinklers. For more information regarding wax coatings, refer to [Bulletin Form No. F_010201](#).
- Allows use from the floor by attaching a length of 1" diameter CPVC tubing to the tool. Ideal for sprinkler cabinets. Refer to [Bulletin F_051808](#).
- The 1/2" NPT Large Orifice Sprinkler is listed and approved for retrofit only when installed in accordance with NFPA 13.
- Approved according to China GB Standard.



TECHNICAL DATA

**MICROMATIC® STANDARD
RESPONSE UPRIGHT
SPRINKLER VK200 (K8.0)**

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
Visit the Viking website for the latest edition of this technical data page: www.vikinggroupinc.com





TECHNICAL DATA

MICROMATIC® STANDARD RESPONSE UPRIGHT SPRINKLER VK200 (K8.0)

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
 Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
 Visit the Viking website for the latest edition of this technical data page: www.vikinggroupinc.com

Approval Chart 1 (UL)

Micromatic® Standard Response Upright Sprinklers
 Maximum 175 PSI (12 bar) WWP

| Sprinkler Base Part Number ¹ | SIN | Thread Size | | Nominal K-Factor | | Overall Length | | Listings and Approvals ³ (Refer also to UL Design Criteria.) | | | | | |
|---|-------|-------------|-------|---------------------|---------------------|-------------------|----|--|-----|--------|-----------------|-----------------|-------------------|
| | | NPT | BSPT | U.S. | metric ² | Inches | mm | cULus ⁴ | VdS | LPCB | CE ⁸ | ⚙ ¹⁰ | China Approval |
| Standard Orifice | | | | | | | | | | | | | |
| 18263 | VK200 | 3/4" | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B4, C5, D3, E6 | A2 | A2, B4 | F3 | F3 | -- |
| 18266 | VK200 | -- | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B4, C5, D3, E6 | A2 | A2, B4 | F3 | F3 | -- |
| 18268 ⁹ | VK200 | 1/2" | 15 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B4, C5, D3, E6 | A2 | A2, B4 | F3 | F3 | -- |
| 20377 ¹¹ | VK200 | -- | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | G3 | -- | -- | -- | -- | G3 |
| NOTICE - Product Below - Limited Availability (Contact Local Viking Office) | | | | | | | | | | | | | |
| 10220 ⁹ | VK200 | 1/2" | 15 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B4, C5, D3, E6 | A2 | A2, B4 | F3 | F3 | -- |
| 10141 | VK200 | 3/4" | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B4, C5, D3, E6 | A2 | A2, B4 | F3 | F3 | -- |
| 10169 | VK200 | -- | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B4, C5, D3, E6 | A2 | A2, B4 | F3 | F3 | -- |
| Approved Temperature Ratings | | | | | | | | Approved Finishes | | | | | |
| A - 135 °F (57 °C), 155 °F (68 °C), 175 °F (79 °C), 200 °F (93 °C), 286 °F (141 °C), and 360 °F (182 °C) | | | | | | | | 1 - Brass, Chrome, White Polyester ^{5,6} and Black Polyester ^{5,6} | | | | | |
| B - 135 °F (57 °C), 155 °F (68 °C), 175 °F (79 °C), and 200 °F (93 °C) | | | | | | | | 2 - Brass, Chrome, White Polyester ⁶ , and Black Polyester ⁶ | | | | | |
| C - 286 °F (141 °C) | | | | | | | | 3 - Brass and Chrome | | | | | |
| D - 500 °F (260 °C) ⁷ | | | | | | | | 4 - Wax-Coated Brass and Wax Over Polyester ⁵ | | | | | |
| E - 155 °F (68 °C), 175 °F (79 °C), 200 °F (93 °C), 286 °F (141 °C), 360 °F (182 °C), and 500 °F (260 °C) ⁷ | | | | | | | | 5 - High Temperature 200 °F (93 °C) Wax Coating (corrosion resistant); maximum ambient temperature allowed at ceiling = 150 °F (65 °C) | | | | | |
| F - 155 °F (68 °C), 175 °F (79 °C), 200 °F (93 °C), 286 °F (141 °C), and 360 °F (182 °C) | | | | | | | | 6 - ENT ⁵ | | | | | |
| G - 155 °F (68 °C), 200 °F (93 °C), and 286 °F (141 °C) | | | | | | | | | | | | | |
| Footnotes | | | | | | | | | | | | | |
| 1. Base part number is shown. For complete part number, refer to Viking's current price schedule. | | | | | | | | | | | | | |
| 2. Metric K-factor shown is for use when pressure is measured in bar. When pressure is measured in kPa, divide the metric K-factor shown by 10.0. | | | | | | | | | | | | | |
| 3. This table shows the listings and approvals available at the time of printing. Check with the manufacturer for any additional approvals. | | | | | | | | | | | | | |
| 4. Listed by Underwriters Laboratories Inc. for use in the U.S. and Canada. | | | | | | | | | | | | | |
| 5. cULus Listed as corrosion resistant. | | | | | | | | | | | | | |
| 6. Other colors are available on request with the same Listings and Approvals as the standard colors. | | | | | | | | | | | | | |
| 7. Sprinklers of Ultra-High temperature rating are intended for use inside ovens, dryers, or similar enclosures with normal operating temperatures above 300 °F (149 °C). Where the ambient temperature around the Ultra-High temperature rated sprinkler is significantly reduced below 300 °F (149 °C), the response time of the Ultra-High temperature rated sprinkler may be severely retarded. | | | | | | | | | | | | | |
| 8. CE Certified, Standard EN 12259-1, EC-certificate of conformity 0832-CPD-2001, and EC-certificate of constancy of performance 0832-CPR-S0021. | | | | | | | | | | | | | |
| 9. The 1/2" NPT Large Orifice Sprinkler is listed and approved for retrofit only when installed in accordance with NFPA 13. | | | | | | | | | | | | | |
| 10. MED Certified, Standard EN 12259-1, EC-certificate 0832-MED-1003. | | | | | | | | | | | | | |
| 11. Approved according to China GB Standard. | | | | | | | | | | | | | |

DESIGN CRITERIA - UL

(Also refer to Approval Chart 1.)

cULus Listing Requirements:

The Viking Micromatic® Standard Response Upright Sprinkler VK200 is cULus Listed as indicated in Approval Chart 1 for installation in accordance with the latest edition of NFPA 13 for standard spray sprinklers.

- Designed for use in Light, Ordinary, and Extra Hazard occupancies.
- The sprinkler installation rules contained in NFPA 13 for standard spray upright sprinklers must be followed.

IMPORTANT: Always refer to Bulletin Form No. F_091699 - Care and Handling of Sprinklers. Also refer to page F_080614 for general care, installation, and maintenance information. Viking sprinklers are to be installed in accordance with the latest edition of Viking technical data, the appropriate standards of NFPA, LPCB, APSAD, VdS or other similar organizations, and also with the provisions of governmental codes, ordinances, and standards, whenever applicable.

| | | |
|---|--|--|
|  | <h2 style="margin: 0;">TECHNICAL DATA</h2> | <h3 style="margin: 0;">MICROMATIC® STANDARD RESPONSE UPRIGHT SPRINKLER VK200 (K8.0)</h3> |
|---|--|--|

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058
 Telephone: 269-945-9501 Technical Services: 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com
 Visit the Viking website for the latest edition of this technical data page: www.vikinggroupinc.com

| Approval Chart 2 (FM) Micromatic® Standard Response Upright Sprinklers Maximum 175 PSI (12 bar) WWP | | | | | | | | |
|--|-------|-------------|-------|--|---------------------|----------------|----|---|
| Sprinkler Base Part Number ¹ | SIN | Thread Size | | Nominal K-Factor | | Overall Length | | FM Approvals ³ (Refer also to Design Criteria below.) |
| | | NPT | BSPT | U.S. | metric ² | Inches | mm | |
| Standard Orifice | | | | | | | | |
| 18268 ⁷ | VK200 | 1/2" | 15 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B2, C1, D3 |
| 18263 | VK200 | 3/4" | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B2, C1, D3 |
| 18266 | VK200 | -- | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B2, C1, D3 |
| 20377 ⁸ | VK200 | -- | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | E4 |
| NOTICE - Product Below - Limited Availability (Contact Local Viking Office) | | | | | | | | |
| 10220 ⁷ | VK200 | 1/2" | 15 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B2, C1, D3 |
| 10141 | VK200 | 3/4" | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B2, C1, D3 |
| 10169 | VK200 | -- | 20 mm | 8.0 | 115.2 | 2-1/4" | 57 | A1, B2, C1, D3 |
| Approved Temperature Ratings A-135 °F (57 °C), 155 °F (68 °C), 175 °F (79 °C), 200 °F (93 °C), 286 °F (141 °C), and 360 °F (182 °C) B - 135 °F (57 °C), 155 °F (68 °C), 175 °F (79 °C), and 200 °F (93 °C) C - 500 °F (260 °C) ⁵ D - 155 °F (68 °C), 175 °F (79 °C), 200 °F (93 °C), 286 °F (141 °C), 360 °F (182 °C), and 500 °F (260 °C) ⁵ E - 155 °F (68 °C), 200 °F (93 °C), 286 °F (141 °C) | | | | Approved Finishes 1 - Brass, Chrome, White Polyester ⁴ , and Black Polyester ⁴ 2 - Wax-Coated Brass (corrosion resistant) 3 - ENT ⁶ 4 - Brass and Chrome | | | | |
| Footnotes | | | | | | | | |
| ¹ Base part number is shown. For complete part number, refer to Viking's current price schedule. ² Metric K-factor shown is for use when pressure is measured in bar. When pressure is measured in kPa, divide the metric K-factor shown by 10.0. ³ This table shows the listings and approvals available at the time of printing. Check with the manufacturer for any additional approvals. ⁴ Other colors are available on request with the same Approvals as the standard colors. ⁵ Sprinklers of Ultra-High temperature rating are intended for use inside ovens, dryers, or similar enclosures with normal operating temperatures above 300 °F (149 °C). Where the ambient temperature around the Ultra-High temperature rated sprinkler is significantly reduced below 300 °F (149 °C), the response time of the Ultra-High temperature rated sprinkler may be severely retarded. ⁶ FM approved as corrosion resistant. ⁷ The 1/2" NPT Large Orifice Sprinkler is listed and approved for retrofit only when installed in accordance with NFPA 13. ⁸ Approved according to China GB Standard. | | | | | | | | |

| |
|---|
| DESIGN CRITERIA - FM (Also refer to Approval Chart 2.) |
| FM Approval Requirements: The Viking Micromatic® Standard Response Upright Sprinkler VK200 is is FM Approved as standard response Non-Storage upright sprinkler as indicated in the FM Approval Guide. For specific application and installation requirements, reference the latest applicable FM Loss Prevention Data Sheets (including Data Sheet 2-0). FM Global Loss Prevention Data Sheets contain guidelines relating to, but not limited to: minimum water supply requirements, hydraulic design, ceiling slope and obstructions, minimum and maximum allowable spacing, and deflector distance below the ceiling. NOTE: The FM installation guidelines may differ from cULus and/or NFPA criteria. |
| IMPORTANT: Always refer to Bulletin Form No. F_091699 - Care and Handling of Sprinklers. Also refer to page F_080614 for general care, installation, and maintenance information. Viking sprinklers are to be installed in accordance with the latest edition of Viking technical data, the appropriate standards of NFPA, FM Global, LPCB, APSAD, VdS or other similar organizations, and also with the provisions of governmental codes, ordinances, and standards, whenever applicable. |