



HMER.EX1299 Check Valves

[Page Bottom](#)

Check Valves

[See General Information for Check Valves](#)

VIKING CORP

210 N INDUSTRIAL PARK RD
HASTINGS, MI 49058 USA

EX1299

Swing type, iron body, Model D-1, sizes 2-1/2 and 3 in.

Swing type, iron body, Models D-1, E-1, sizes 2-1/2 in. rated for 300 psig.

Swing type, iron body, Model D-2, sizes 4 and 6 in.

Swing type, iron body, Model E-1, sizes 2-1/2 in.

Swing type, iron body, Model E-2, sizes 3 and 8 in.

Swing type, iron body, Model F-1, sizes 3, 4, 6 and 8 in. rated for 300 psig.

Swing type, iron body, Model G-1, sizes 3, 4, 6 and 8 in. rated for 300 psig.

Swing type

, Model L-1, Groove/Groove, sizes 1-1/2 and 2 in. rated for 250 psig.

Swing type , Model K-1, NPT threaded, sizes 1-1/2 and 2 in. rated for 250 psig.

Swing type , Model M-2, Groove/Groove, size 4 in. rated for 250 psig.

Model CF300, sizes 2, 2-1/2, 3, 4, 5, 6, 8, 10 and 12 in. (50.8, 63.5, 76.2, 101.6, 127, 139.7, 203.2, 254 and 304.8mm), with rubber faced checks for working pressures not exceeding 300 psig (2068Kpa). Installation - horizontal or vertical.

Model CG300, sizes 2-1/2, 3, 4, 5, 6, 8, 10 and 12 in. (63.5, 76.2, 101.6, 127, 139.7, 203.2, 254 and 304.8mm), with rubber faced checks for working pressures not exceeding 300 psig (2068Kpa). Installation - horizontal or vertical.

[Last Updated](#) on 2011-07-27

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2011 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2011 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.





HMER7.EX1299 Check Valves Certified for Canada

[Page Bottom](#)

Check Valves Certified for Canada

[See General Information for Check Valves Certified for Canada](#)

VIKING CORP

EX1299

210 N INDUSTRIAL PARK RD
HASTINGS, MI 49058 USA

Swing type, iron body, Models D-1, E-1, sizes 2-1/2 in. rated for 300 psig.

Swing type, iron body, Model F-1, sizes 3, 4, 6 and 8 in. rated for 300 psig.

Swing type, iron body, Model G-1, sizes 3, 4, 6 and 8 in. rated for 300 psig.

Swing type, Model M-2, Groove/Groove, size 4 in. rated for 250 psig.

[Last Updated](#) on 2011-08-11

[Questions?](#)

[Print this page](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2011 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2011 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

