

TABLE OF CONTENTS

TotalPac®3 – Introduction.....K-1
 TotalPac®3 – Preaction Systems.....K-2
 TotalPac®3 – Deluge, Wet, and Dry Systems.....K-3
 TotalPac®3 – Firecycle® III and SureFire® Systems.....K-4
 TotalPac®3 – System Options / Release Control Panel OptionsK-5
 TotalPac®3 – Air Supply Options.....K-6
 TotalPac®3 – Terms and ConditionsK-7

Notes

1. Refer to Viking technical data pages for complete product specifications. You may print or download technical data by visiting www.vikinggroupinc.com.
2. List prices effective January 20, 2020. Supersedes January 2019 list price book.
3. All sales by Viking are subject to the terms & conditions found on the last page of this book.

SureFire® and Firecycle® are registered trademarks of The Viking Corporation.



NEW - TOTALPAC®3 Integrated Fire Protection Systems

Introduction:

Pricing of the TotalPac3 Product Line are priced by adding various options together until a complete unit is obtained.

A basic system now includes the system valve, its releasing trim and its supporting assembly, whether it is a skid, a remote-controlled T3ACCELE1D

cabinet without control panel or a self-contained unit with control panel. These are all included under a single part number.

The price list now resembles a matrix which facilitates its use. It is divided into 10 sections and is consistent with the User Manuals:

1. Preaction Systems (Non, Single & Double Interlock);
2. Deluge Systems;
3. Wet Pipe Systems;
4. Dry Pipe Systems (both normal & HP);
5. Cycling Systems (Firecycle III);
6. Surefire Systems.

Followed by:

7. System Options (Shut-off Valve, FD Connection, etc.);
8. VFR-400 Control Panel Options (zones, relays, batteries, etc.);
9. Air Supplies (the usual 4 styles – A,B,C & D), and then,
10. Air Supply Options (Dehydrator, Accelerator, etc.).

To order a TotalPac3:

First, select the type of system required (preaction, deluge, dry, etc...). Then, choose the style of system required (skid mounted, remote controlled or self-contained) and its release system (electric, pneumatic, etc.). Finally, follow this line to the proper part number under the column of the system size (TotalPac3 units are available in 6 sizes: 1½", 2", 3", 4", 6" and 8" diam.). This is the part number that should be ordered. Add the required system options to complete your order.

The Configuration/order Form (doc. # FM-08CD-0-17-D) uses the same format as the price list.

Provided are additional details on the three styles of TotalPac3 units available:

- **Skid Mounted Units:** Skid Units include only the basic Valve Trim and its required Releasing Trim. Electrical components have to be wired on-site by the contractor. Grooved or flanged connections are provided for water supply, drain and system riser. Remote releasing control panel and air compressor (if required) have to be purchased separately (*they are not provided by FireFlex Systems Inc.*) and installed by the contractor on-site. Every Skid Unit is supplied with its own User Manual and is also serialized for after sales support. Serial Number format is TOTSxxxx.

- **Remote Controlled Units:** These units are composed of the basic Valve, Trim and Releasing Trim, enclosed in a sturdy 14-gauge steel cabinet with one or two front doors and a contractor field wiring junction box on top of the cabinet. All electrical components are factory wired to the field wiring terminal strip. Wiring schematics are included on the inside of the front doors. Grooved or flanged connections are provided for water supply, drain and system riser. Four different air supply options are available, and factory assembled. Remote releasing control panel, if required, has to be purchased separately (*they are not provided by FireFlex Systems Inc.*) and installed by the contractor on-site. Every Remote-Controlled Unit is supplied with a User Manual and is serialized for after sales support. Serial Number format is TOT3xxxx.

- **Self-Contained Units:** These units are composed of a Remote-Controlled Unit as described above, plus a Release Control Panel Enclosure mounted on top of the cabinet. All electrical components are factory wired to the Viking VFR-400 Control Panel, with wiring schematics included on the inside of the front doors. Grooved or flanged connections are provided for water supply, drain and system riser. Four different air supply options are available, and factory assembled.

Every self-contained unit is supplied with a User Manual and is serialized for after sales support. Serial Number format is TOT3xxxx.

Refer to the Price List for various options available with each style & system type.

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Preaction Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
PREACTION NON INTERLOCK	Skid Mounted	Electric	T3PNELSK15 \$22,881	T3PNELSK20 \$25,637	T3PNELSK30 \$28,659	T3PNELSK40 \$34,020.80	T3PNELSK60 \$39,803	N/A
		Pneumatic	T3PNPNSK15 \$21,314	T3PNPNSK20 \$23,970	T3PNPNSK30 \$26,987	T3PNPNSK40 \$32,354	T3PNPNSK60 \$38,153	N/A
	Without Panel (Remote)	Electric	T3PNELNP15 \$31,325	T3PNELNP20 \$34,688	T3PNELNP30 \$37,675	T3PNELNP40 \$42,992	T3PNELNP60 \$48,727	T3PNELNP80 \$74,878
		Pneumatic	T3PNPNNP15 \$29,758	T3PNPNNP20 \$32,942	T3PNPNNP30 \$35,991	T3PNPNNP40 \$40,481	T3PNPNNP60 \$46,250	T3PNPNNP80 \$73,330
	With VFR-400 – 120V/60Hz	Electric	T3PNELWP15 \$38,436	T3PNELWP20 \$41,805	T3PNELWP30 \$44,797	T3PNELWP40 \$49,579	T3PNELWP60 \$55,242	T3PNELWP80 \$82,816
			T3PNELWP15 \$38,436	T3PNELWP20 \$41,805	T3PNELWP30 \$44,797	T3PNELWP40 \$49,579	T3PNELWP60 \$55,242	T3PNELWP80 \$82,816
PREACTION SINGLE INTERLOCK	Skid Mounted	Electric	T3PSELSK15 \$20,572	T3PSELSK20 \$23,380	T3PSELSK30 \$26,402	T3PSELSK40 \$31,770	T3PSELSK60 \$37,558	N/A
		Pneumatic	T3PSPNSK15 \$20,412	T3PSPNSK20 \$23,481	T3PSPNSK30 \$26,492	T3PSPNSK40 \$31,871	T3PSPNSK60 \$37,659	N/A
	Without Panel (Remote)	Electric	T3PSELNP15 \$29,074	T3PSELNP20 \$32,448	T3PSELNP30 \$35,435	T3PSELNP40 \$40,364	T3PSELNP60 \$46,156	T3PSELNP80 \$71,389
		Pneumatic	T3PSPNNP15 \$29,158	T3PSPNNP20 \$32,482	T3PSPNNP30 \$35,536	T3PSPNNP40 \$40,031	T3PSPNNP60 \$46,600	T3PSPNNP80 \$71,839
	With VFR-400 – 120V/60Hz	Electric	T3PSELWP15 \$35,600	T3PSELWP20 \$38,901	T3PSELWP30 \$42,023	T3PSELWP40 \$45,770	T3PSELWP60 \$52,108	T3PSELWP80 \$79,322
			T3PSELWP15 \$35,600	T3PSELWP20 \$38,901	T3PSELWP30 \$42,023	T3PSELWP40 \$45,770	T3PSELWP60 \$52,108	T3PSELWP80 \$79,322
PREACTION DOUBLE INTERLOCK <small>Note: NYFD Accepted & FM Approved for use in refrigerated areas only.</small>	Skid Mounted	Elect-Pnelect.	T3PDPSK15 \$20,629	T3PDPSK20 \$23,379	T3PDPSK30 \$26,401	T3PDPSK40 \$31,768	T3PDPSK60 \$37,562	N/A
		Elect-Pneum.	T3PDPASK15 \$21,186	T3PDPASK20 \$24,160	T3PDPASK30 \$27,171	T3PDPASK40 \$32,544	T3PDPASK60 \$38,338	N/A
		Pneum-Pneum.	T3PDPPSK15 \$20,732	T3PDPPSK20 \$24,079	T3PDPPSK30 \$27,084	T3PDPPSK40 \$32,468	T3PDPPSK60 \$38,251	N/A
	Without Panel (Remote)	Elect-Pnelect.	T3PDEPNP15 \$29,072	T3PDEPNP20 \$32,452	T3PDEPNP30 \$35,433	T3PDEPNP40 \$40,446	T3PDEPNP60 \$46,233	T3PDEPNP80 \$71,388
		Elect-Pneum.	T3PDPANP15 \$29,848	T3PDPANP20 \$33,217	T3PDPANP30 \$36,215	T3PDPANP40 \$40,609	T3PDPANP60 \$46,031	T3PDPANP80 \$73,075
		Pneum-Pneum.	T3PDPPNP15 \$29,175	T3PDPPNP20 \$32,128	T3PDPPNP30 \$35,309	T3PDPPNP40 \$39,423	T3PDPPNP60 \$45,582	T3PDPPNP80 \$73,444
	With VFR-400 – 120V/60Hz	Elect-Pnelect.	T3PDEPWP15 \$35,688	T3PDEPWP20 \$38,978	T3PDEPWP30 \$42,089	T3PDEPWP40 \$46,708	T3PDEPWP60 \$52,483	T3PDEPWP80 \$79,326
		Elect-Pneum.	T3PDPAWP15 \$36,148	T3PDPAWP20 \$39,247	T3PDPAWP30 \$42,211	T3PDPAWP40 \$46,493	T3PDPAWP60 \$52,485	T3PDPAWP80 \$80,563

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Deluge Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
DELUGE	Skid Mounted	Electric	T3DEELSK15 \$19,722	T3DEELSK20 \$23,013	T3DEELSK30 \$25,850	T3DEELSK40 \$31,213	T3DEELSK60 \$35,915	N/A
		Pneumatic	T3DEPNK15 \$19,734	T3DEPNK20 \$23,108	T3DEPNK30 \$25,939	T3DEPNK40 \$31,308	T3DEPNK60 \$36,010	N/A
		Hydraulic	T3DEHYSK15 \$17,758	T3DEHYSK20 \$20,622	T3DEHYSK30 \$23,453	T3DEHYSK40 \$28,816	T3DEHYSK60 \$33,524	N/A

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
DELUGE	Without Panel (Remote)	Electric	T3DEELNP15 \$28,746	T3DEELNP20 \$31,924	T3DEELNP30 \$34,804	T3DEELNP40 \$13	T3DEELNP60 \$44,113	T3DEELNP80 \$67,788
		Pneumatic	T3DEPNNP15 \$28,774	T3DEPNNP20 \$31,597	T3DEPNNP30 \$34,595	T3DEPNNP40 \$38,821	T3DEPNNP60 \$44,799	T3DEPNNP80 \$68,266
		Hydraulic	T3DEHYNP15 \$26,366	T3DEHYNP20 \$29,713	T3DEHYNP30 \$32,525	T3DEHYNP40 \$37,551	T3DEHYNP60 \$42,229	T3DEHYNP80 \$67,057
	With VFR-400 – 120V/60Hz	Electric	T3DEELWP15 \$35,339	T3DEELWP20 \$38,146	T3DEELWP30 \$41,026	T3DEELWP40 \$45,770	T3DEELWP60 \$50,448	T3DEELWP80 \$75,721

Wet Pipe Systems:

WET PIPE	Skid Mounted	N/A	N/A	N/A	T3WETESK30 \$13,135	T3WETESK40 \$16,195	T3WETESK60 \$18,266	N/A
	In Cabinet	N/A	N/A	N/A	T3WETENP30 \$22,031	T3WETENP40 \$25,058	T3WETENP60 \$27,106	T3WETENP80 \$34,450
System Options:	Constant Pressure Trim	T3CONPRESS POA		Excess Pressure Pump 1/3 HP (120V/60Hz)		T3WETEPP03 POA		
	Retard Chamber	T3WETRET00 POA		Excess Pressure Pump 1/2 HP (120V/60Hz)		T3WETEPP05 POA		

Dry Pipe Systems:

DRY PIPE 175 psi	Skid Mounted	N/A	N/A	N/A	N/A	T3DRYESK40 \$20,238	T3DRYESK60 \$23,539	N/A
	In Cabinet (Remote)	N/A	N/A	N/A	N/A	T3DRYENP40 \$29,057	T3DRYENP60 \$32,335	N/A
HP DRY PIPE 250 psi	Skid Mounted	N/A	T3DHPESK15 POA	T3DHPESK20 POA	T3DHPESK30 POA	T3DHPESK40 POA	T3DHPESK60 POA	N/A
	In Cabinet (Remote)	N/A	T3DHPENP15 \$29,079	T3DHPENP20 \$32,838	T3DHPENP30 \$36,286	T3DHPENP40 \$41,367	T3DHPENP60 \$47,875	T3DHPENP80 \$69,119

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Firecycle® III Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
PREACTION SINGLE INTERLOCK	Skid Mounted	Firecycle III	T3FSINSK15 \$28,881	T3FSINSK20 \$33,331	T3FSINSK30 \$36,964	T3FSINSK40 \$43,190	T3FSINSK60 \$50,202	N/A
	Without Panel (Remote)		T3FSINNP15 \$37,454	T3FSINNP20 \$42,298	T3FSINNP30 \$45,913	T3FSINNP40 \$52,082	T3FSINNP60 \$59,026	T3FSINNP80 \$78,845
	With VFR-400 – 120V/60Hz		T3FSINWP15 \$45,308	T3FSINWP20 \$50,366	T3FSINWP30 \$54,386	T3FSINWP40 \$59,846	T3FSINWP60 \$66,182	T3FSINWP80 \$86,359
PREACTION DOUBLE INTERLOCK	Skid Mounted	Firecycle III	T3FDOUSK15 \$28,881	T3FDOUSK20 \$33,331	T3FDOUSK30 \$36,964	T3FDOUSK40 \$43,190	T3FDOUSK60 \$50,202	N/A
	Without Panel (Remote)		T3FDOUNP15 \$37,454	T3FDOUNP20 \$42,298	T3FDOUNP30 \$45,913	T3FDOUNP40 \$52,082	T3FDOUNP60 \$59,026	T3FDOUNP80 \$78,845
	With VFR-400 – 120V/60Hz		T3FDOWP15 \$45,308	T3FDOWP20 \$50,366	T3FDOWP30 \$54,386	T3FDOWP40 \$59,846	T3FDOWP60 \$66,182	T3FDOWP80 \$86,416

SureFire® Fail Safe Preaction Systems:

SYSTEM TYPE	STYLE	RELEASE	SYSTEM SIZE					
			1½"	2"	3"	4"	6"	8"
PREACTION SINGLE INTERLOCK	Skid Mounted	Surefire	T3SFSISK15 \$26,814	T3SFSISK20 \$30,065	T3SFSISK30 \$33,329	T3SFSISK40 \$39,102	T3SFSISK60 \$45,323	N/A
	Without Panel (Remote)		T3SFSINP15 \$35,454	T3SFSINP20 \$39,076	T3SFSINP30 \$42,294	T3SFSINP40 \$48,022	T3SFSINP60 \$54,185	T3SFSINP80 \$76,851
	With VFR-400 - 120V/60Hz		T3SFSIWP15 \$42,588	T3SFSIWP20 \$46,205	T3SFSIWP30 \$49,422	T3SFSIWP40 \$54,784	T3SFSIWP60 \$60,998	T3SFSIWP80 \$83,856
PREACTION DOUBLE INTERLOCK <small>Note: NYFD & FM Approved for use in refrigerated areas only.</small>	Skid Mounted	Surefire	T3SFDOSK15 \$26,814	T3SFDOSK20 \$29,876	T3SFDOSK30 \$33,123	T3SFDOSK40 \$38,866	T3SFDOSK60 \$45,063	N/A
	Without Panel (Remote)		T3SFDONP15 \$35,263	T3SFDONP20 \$38,879	T3SFDONP30 \$42,094	T3SFDONP40 \$47,799	T3SFDONP60 \$52,899	T3SFDONP80 \$76,851
	With VFR-400 - 120V/60Hz		T3SFDOWP15 \$42,399	T3SFDOWP20 \$45,993	T3SFDOWP30 \$49,216	T3SFDOWP40 \$54,493	T3SFDOWP60 \$60,704	T3SFDOWP80 \$83,835

NEW - TOTALPAC®3 Integrated Fire Protection Systems

System Options:

Shut-off Valve & Sight Glass (Not available for Wet & Dry Pipe systems)	T3SHUTV015 \$1,650	T3SHUTV020 \$1,891	T3SHUTV030 \$2,120	T3SHUTV040 \$2,186	T3SHUTV060 \$2,606	N/A
Fire Department Connection (Always on right hand side)	T3FIRDPT15 \$535	T3FIRDPT20 \$562	T3FIRDPT30 \$629	T3FIRDPT40 \$722	T3FIRDPT60 \$902	N/A
Semi-Flanged Inlets & Outlet:	T3SEMFLG15 \$1,382	T3SEMFLG20 \$1,262	T3SEMFLG30 \$1,470	T3SEMFLG40 \$1,666	T3SEMFLG60 \$1,967	T3SEMFLG80 \$2,705
Full-Flanged Inlets & Outlet:	PRICE ON REQUEST ONLY					
Elevator Option	T3ELEVATOR			PRICE ON REQUEST ONLY SPECIAL CONDITIONS APPLY		
Anti Column device	T3ANTCOLD1			\$1,381		
Galvanized Main Inlet & Riser	T3GALVOPTI			\$1,288		
OSHPD Seismic Option	T3SISMIQ00			\$1,604.56		

VFR-400 Releasing Panel Options:

Available with 120V / 60Hz or 220V / 50Hz

Emergency Batteries:	Standard Systems:	7 AH (Included with unit, use for replacement only) T3BAT02407 \$284	12 AH (FM's 90 Hrs Stand-by) T3BAT02412 \$503
	Surefire & Firecycle III Systems:	12 AH (Included with unit, use for replacement only) T3BAT02412 \$503	17 AH (FM's 90 Hrs Stand-by) T3BAT02417 POA
VFR-400 Panel Options:	L.A. Auxiliary Contacts – T3LAOPTION \$73	Chicago Auxiliary Contacts – T3CHOPTION \$73	NYFD Kit – T3VFRPNYOP \$393 (Class A Modules included do not duplicate)
	Rem. Annunciator – T3VFRP4410 \$1,235		Relay Module – T3OPTARM44 \$1,386
	Class "A" Initiating Ccts – T3VFRPCA2Z \$485	Class "A" Indicating Ccts – T3VFRPCAM2 \$373	

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Air Supplies:

Air Supplies for Skids (Trim only – NO compressor)	For Preaction – Surefire Firecycle III & HP Dry Pipe	Deluge Pneum. Release	Single Pneum. & Double Int'lk Pneum-Pneum. Release
	T3ARTITSK1 \$1,196	T3ARTITSK2 \$1,010	T3ARTITSK3 \$1,887

Air Supplies for Cabinets	Style "A" (Tankless Air Compressor)						Style "B"	Style "C"	Style "D"
	1/6 HP	1/3 HP	1/2 HP	1 HP	1 1/2 HP (8" unit only)	2 HP (8" unit only)	Air Pressure Maintenance Device for Sprinkler Piping	Air Pressure Maintenance Device for Pilot Line	Air Shut-off Valve, Pressure Gauge, & Pressure Switch Only
120 V / 60 Hz:	T3AIRK0A02 \$5,004	T3AIRK0A03 \$5,954	T3AIRK0A05 \$6,718	T3AIRK0A10 \$8,044	T3AIRK0A15 \$10,948	T3AIRK0A20 POA	T3AIRK0B00 \$2,258	T3AIRK0C00 \$2,303	T3AIRK0D00 \$649
220V / 50 Hz	T3AIRK2A02 \$5,846	T3AIRK2A03 \$6,890	T3AIRK2A05 \$8,414	T3AIRK2A10 \$9,660	T3AIRK2A15 POA	N/A			

Notes:

1. Style "A" Air Supply cannot be mixed with Style "B".
2. In the case of a Preaction System with Pilot Line, order either one Style "A" with one Style "C" if you need a tankless air compressor in the cabinet for the sprinklers piping, OR, one Style "B" and one Style "C" if you want both air supplies to be located outside the system cabinet.
3. Pilot Line Air Supply will always be provided by a source located outside the TP3 Cabinet, supplied by others (not FireFlex).
4. Air Supply Style "D" is used when air supply and regulation is provided by others, as is the case with plant air, or with refrigerated areas when a dry air supply as described in NFPA-13 is required.
5. 1 HP Air compressor available on 4" & 6" systems only.
6. 1 ½ HP & 2 HP Air compressors available on 8" systems only.

Air Supply Options:

Accelerator E-1	Without Anti-flood Device (For Preaction, Pneum. Rel. Pilot Line & HP Dry only)	With Anti-flood Device (For Standard Dry Pipe only)
		T3ACCELE1P \$3,378
Dehydrator	T3DEHYDRAT \$3,704	

NEW - TOTALPAC®3 Integrated Fire Protection Systems

Terms and Conditions

This price list should be used in conjunction with the VIKING TotalPac3 Configuration/Order Form (FM-08CD-0-17-D latest revision).

All prices are NET and are indicated in US dollars, FOB our plant in Boisbriand, Quebec (Canada). For special discounts or configurations, please contact FireFlex Systems Customer Service.

Listings and Approvals: Most TotalPac3 Configurations in our product range are cULus Listed & FM Approved as factory-built complete units. Any system modification, to meet project specs or local AHJ requirements, ordered as a custom-built system will void the Listing on the TotalPac3 as an assembly but individual components Listings/Approvals will remain.

Special Order Item: Every TotalPac3 Unit is a Special-Order Item which is built to order. It can therefore not be cancelled nor returned without FireFlex Systems explicit consent or authorization.

Returns & Credits: The following conditions shall apply to all TotalPac3 units returned for credit:

- Unit(s) shall be of current design, three months old maximum after shipping date from the factory;
- Unit(s) shall still be in its (their) original packing (never unpacked), unused and not installed. Any unit not in this condition is subject to additional charges to cover inspection, handling, repackaging, refurbishment, or any other expenses incurred by FireFlex Systems in accepting the unit(s).
- The customer is responsible for freight charges to return overstocked unit(s), unit(s) no longer required, or ordered by mistake. Any damage incurred in transit will be deducted from the credit value.

NOTE: An RMA Number shall be obtained from FireFlex' Customer Service PRIOR to returning any unit. Please provide unit(s) serial number(s) as indicated on the shipping label of the unit(s) (format: TOTSxxxx or TOT3xxxx) as well as the address for us to make arrangements for pick-up.

Please note that a minimum restocking charge of \$ 1,500.00 is applicable on all TotalPac3 returns. Systems older than 3 months after date of shipment will NOT be accepted for credit.

Upon receiving returned unit(s), FireFlex Systems will inspect each unit. If any damage is found, the credit amount will be adjusted accordingly.

Contractor must ascertain the unit is returned in its original packing, including the internal plastic liner. This liner protects the unit finish against abrasion damage during transport.

Warranty: FireFlex Systems provides warranty on all TotalPac3 Units for a period of 1 (one) year from time of shipping. Warranty does not cover labor. We will replace any component found defective at no charge during this period but will NOT reimburse labor charges incurred by the contractor. In the case of unauthorized modification of, or tampering with the unit, the warranty is void.

The warranty on batteries warranty is limited to 3 (three) months. Refer to the terms of our Standard Warranty for all details (provided with every TotalPac3 User's Manual).