



Viking Foam Suppression Systems | FM Approved and UL Listed

For all your project needs, proven quality from one trusted source

Viking foam suppression systems are designed to limit fire damage in many challenging and high risk applications such as warehouses, production areas, oil and chemical processing facilities and chemical plants. A typical foam system consists of the following components that are tested, approved and/or listed together:

- Foam bladder tank
- Proportioning device
- Foam concentrate
- Discharge device – compatible, tested and approved with specific foam concentrates in accordance with FM5130 and/or UL162

Features and advantages of Viking's Low Expansion Foam System:

- Assured functionality and performance due to extensive system testing.
- Compliant with NFPA 11 and FM Global Data Sheet 4-12.
- Bladder tanks with 232 psi rating for high pressure systems.
- ASME bladder tank design codes with CE marking.
- Wide range of foam and discharge devices with extensive fields of use.
- A complete foam system package from one trusted source.

Contact your local Viking SupplyNet team to place an order today!

The Viking Corporation

210 N. Industrial Park Drive, Hastings, MI 49058

Telephone: (877) 384-5464

www.vikinggroupinc.com

Trusted above all.™

System components:
Foam Bladder Tanks:
 25 - 4,000 USG Vertical
 50 - 5,250 USG Horizontal
 175 psi & 232 psi versions

Proportioning Devices:
 2" to 8" Ratio Controller
 3" to 8" ILBP

Foam Concentrates:
 AFFF 1% S C6
 AFFF 3% S C6
 ARC 3X3S C6
 FP 3%
 AFFF 3% M C6

Discharge Devices:
 Foam-Water Sprinkler
 Aircraft Hangar Grate Nozzle
 Foam Chambers
 Foam Makers
 Helideck Nozzle

Listings/ Approvals*:
 FM Approved (FM5130)
 UL Listed (UL162)
 ASME Sec VIII Div1

* For all applicable approvals, please refer to the technical documentation or contact your local Viking sales office.

MKT-2002

