

May 18, 2009




TECHNICAL DATA

4" MODEL M-2 CHECK VALVE  
FRICTION LOSS CHART

The Viking Corporation, 210 N Industrial Park Drive, Hastings MI 49058  
Telephone: 269-945-9501 Technical Services 877-384-5464 Fax: 269-818-1680 Email: techsvcs@vikingcorp.com

FOR USE WITH ENGLISH PRACTICAL SYSTEM  
Where Flow is Measured in GPM and Pressure is Measured in PSI

Graph is for reference purposes.



Friction Loss for the 4" Viking Model M-2 Check Valve is equivalent to 15 feet of 4" Schedule 40 (id = 4.026") Pipe (C = 120).

To calculate friction loss for the 4" (id = 4.026") Viking M-2 Check Valves at a specific flow, use the following formula:

$$P_{\text{PSI}} = \left( \frac{4.52 \times Q^{1.85}}{C^{1.85} \times 4.026^{4.87}} \right) \times 15$$

Where P = Friction Loss (PSI)  
Q = Flow in GPM  
C = Constant (=120)