

## FM Approved EG-100 ESFR Sprinkler Guards protect in-rack storage

Viking's ESFR sprinkler guards are now FM Approved to protect in-rack ESFR sprinklers from damage in areas with high activity, such as storage applications, where damage to low elevation sprinklers is likely to occur. The ESFR sprinkler guards feature a hinged clamshell design with a hardwire cage that completely surrounds the sprinkler.

Features and advantages of Viking's ESFR sprinkler guard:

- FM Approved for use in in-rack storage applications
- Hard-wired steel cage design surrounds the ESFR sprinkler in its entirety, protecting it from damage
- Effective in areas where sprinklers are installed at a low elevation or near a high degree of human or mechanical activity
- FM Approved for use with Viking ESFR sprinkler models VK506, VK510, and VK514
- Available in a 3-7/8" (98 mm) length and 3-1/2" (90 mm) diameter
- Made from carbon steel material and available in chrome or painted red finishes

For more information, please contact your Viking sales representative or visit our website at **vikinggroupinc.com**.

## **TECHNICAL SPECIFICATIONS**

Model Number: EG-100

Base Part Number: 24988F, 24988M/R

**Listings/Approvals:** FM Approved

Finish: Chrome, Red

Item Price Group: V206

Occupancy/Hazard: Storage/Non-Storage

Technical Datasheet: F\_061520

**Dimensions:** 3-7/8" length 3-1/2" diameter

1" NPT

## **DIGITAL TOOLS**



Size:

Viking's revolutionary Sprinkler Selector ensures that you can find the right sprinkler for the job — every time. Get started by visiting webtools.vikingcorp.com/sprinklerselector.

MKT-0008

General reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and consult with the AHJ.



