

Residential Sprinkler Quick Reference Guide

This guide is intended for general reference only. Prior to the design, layout, and/or installation of any sprinkler system, please refer to Viking's technical documentation and always consult with the AHJ. Viking makes no representation or warranty as to whether following this guide will satisfy any rule or requirement. Please visit www.vikinggroupinc.com for the most current technical data and product specifications. All products must be installed in accordance with the manufacturer's current installation instructions. Viking reserves the right to change product specifications at any time without notice and without incurring obligation.



Pendent and Recessed Pendent Sprinklers

Recessed adjustment up to 5/8" (16 mm)

3.0 (43) K-factor



VK470, Part No. 17147
Technical datasheet F_061011

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Enables two-head design with flows less than 20 gpm (75,7 lpm)
- Can optimize NFPA 13 residential designs when combined with larger K-factor residential sprinklers
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	Horizontal Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	8 (30)	7.1 (49)
14 x 14 (4,3x4,3)	10 (38)	11.1 (77)
15 x 15 (4,6x4,6)	12 (45)	16 (110)
16 x 16 (4,9x4,9)	13 (49)	18.8 (129)

4.3 (62) K-factor



VK430, Part No. 09530
Technical datasheet F_082095

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Continually listed by UL since 1995
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	12 (45)	7.8 (54)
14 x 14 (4,3x4,3)	13 (49)	9.1 (63)
16 x 16 (4,9x4,9)	13 (49)	9.1 (63)
18 x 18 (5,5x5,5)	17 (64)	15.6 (108)
20 x 20 (6,1x6,1)	21 (80)	23.9 (164)

4.9 (71) K-factor



VK468, Part No. 13637
Technical datasheet F_012706

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	13 (49)	7.0 (48)
14 x 14 (4,3x4,3)	13 (49)	7.0 (48)
16 x 16 (4,9x4,9)	13 (49)	7.0 (48)
18 x 18 (5,5x5,5)	17 (64)	12.0 (83)
20 x 20 (6,1x6,1)	20 (76)	16.7 (115)

5.2 (75) K-factor



VK466, Part No. 13781
Technical datasheet F_019406

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	14 (53)	7.2 (50)
14 x 14 (4,3x4,3)	14 (53)	7.2 (50)
16 x 16 (4,9x4,9)	14 (53)	7.2 (50)
18 x 18 (5,5x5,5)	17 (64)	10.7 (74)
20 x 20 (6,1x6,1)	20 (76)	14.8 (1.02)

5.8 (84) K-factor



VK472, Part No. 16130
Technical datasheet F_121409

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	16 (61)	7.6 (52)
14 x 14 (4,3x4,3)	16 (61)	7.6 (52)
16 x 16 (4,9x4,9)	16 (61)	7.6 (52)
18 x 18 (5,5x5,5)	17 (64)	8.6 (59)
20 x 20 (6,1x6,1)	21 (80)	13.1 (90)

7.4 (107) K-factor



VK458, Part No. 13230
Technical datasheet F_042005

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	20 (76)	7.3 (50)
14 x 14 (4,3x4,3)	20 (76)	7.3 (50)
16 x 16 (4,9x4,9)	20 (76)	7.3 (50)
18 x 18 (5,5x5,5)	22 (83)	8.8 (61)
20 x 20 (6,1x6,1)	24 (91)	10.5 (73)

*Flows shown for 155°F/68°C; see technical datasheet for flows at 175°F/79°C.

All application data is for smooth, flat, horizontal ceilings unless otherwise noted, and is per each sprinkler's cULus Listing for systems designed to NFPA 13D or NFPA 13R requiring a 0.05 gpm/ft² density.

Trusted above all.™



Flat Plate Concealed Pendent Sprinklers

Cover Plate Temp = 135°F/57°C and 165°F/74°C; Adjustment up to 1/2" (13 mm)

3.0 (43) K-factor



VK496, Part No. 22773
Technical datasheet F_112817

- Sprinkler temp = 155°F/68°C and 200°F/93°C*
- Enables two-head design with flows less than 20 gpm (76 lpm)
- Can optimize NFPA 13 residential designs when combined with larger K-factor residential sprinklers

Coverage Area ft (m)	Horizontal Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	8 (30)	7.1 (49)
14 x 14 (4,3x4,3)	12 (45)	16 (110)
16 x 16 (4,9x4,9)	15 (56)	25 (172)

*UL Listed flow rates are identical for both temperature ratings.

4.9 (71) K-factor



VK494, Part No. 20759
Technical datasheet F_012116

- Sprinkler temp = 155°F/68°C and 200°F/93°C*
- Intermediate temperature models provide greater installation flexibility
- Available with either standard, large, or square cover plate
- Available with ENT plating (Nickel PTFE) for corrosion resistance
- Available with stainless steel cover plate

12 x 12 (3,7x3,7)	13 (49)	7.0 (48)
14 x 14 (4,3x4,3)	13 (49)	7.0 (48)
16 x 16 (4,9x4,9)	13 (49)	7.0 (48)
18 x 18 (5,5x5,5)	17 (64)	12.0 (83)
20 x 20 (6,1x6,1)	20 (76)	16.7 (115)

*UL Listed flow rates are identical for both temperature ratings.

5.8 (84) K-factor



VK498, Part No. 22037
Technical datasheet F_112817

- Sprinkler temp = 155°F/68°C and 200°F/93°C*
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	16 (61)	7.6 (52)
14 x 14 (4,3x4,3)	16 (61)	7.6 (52)
16 x 16 (4,9x4,9)	16 (61)	7.6 (52)
18 x 18 (5,5x5,5)	17 (64)	8.6 (59)
20 x 20 (6,1x6,1)	20 (76)	11.9 (82)

*UL Listed flow rates are identical for both temperature ratings.

Flat Plate Concealed Sidewall Sprinklers

Cover plate temp = 135°F/57°C

4.0 (58) K-factor



VK480, Part No. 16116AC
Technical datasheet F_121609

- Sprinkler temp = 165°F/74°C and 205°F/96°C
- Use cover plate 16207MA/W
- White cover plate is standard; can be custom painted to match any decor
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	4-6" (102mm-152mm) From Ceiling		6-12" (152mm-305mm) From Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	11 (42)*	7.6 (52)	12 (46)**	9.0 (62)
14 x 14 (4,3x4,3)	13 (49)*	10.6 (73)	14 (53)**	12.3 (84)
16 x 16 (4,9x4,9)	16 (61)*	16.0 (110)	16 (61)**	16.0 (110)
16 x 18 (4,9x5,5)	17 (64)*	18.1 (125)	18 (68)**	20.3 (140)

*Centerline of the sprinkler located 4-3/8" (111mm) to 6-3/8" (162mm) below the ceiling.

**Centerline of the sprinkler located 6-3/8" (162mm) to 12-3/8" (314mm) below the ceiling.

***Flows and pressures shown above refer to the 165° temperature rating. Please consult the product technical datasheet for flows and pressures of the 205° temperature rating.

5.8 (84) K-factor



VK490, Part No. 20409
Technical datasheet F_032116

- Sprinkler temp = 165°F/74°C and 205°F/96°C
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft²)

Coverage Area ft (m)	4-6" (102mm-152mm) From Ceiling		6-12" (152mm-305mm) From Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3.7 x 3.7)	16 (70)*	7.6 (52)	17 (64)**	8.6 (59)
14 x 14 (4.3 x 4.3)	17 (64)*	8.6 (59)	17 (64)**	8.6 (59)
16 x 16 (4.9 x 4.9)	18 (68)*	9.6 (66)	19 (72)**	10.7 (74)
16 x 18 (4.9 x 5.5)	21 (80)*	13.1 (90)	21 (80)**	13.1 (90)
16 x 20 (4.9 x 6.1)	23 (87)*	15.7 (108)	26 (98)**	20.1 (139)
16 x 22 (4.9 x 6.7)	31 (117)*	28.6 (197)	31 (117)**	28.6 (197)
18 x 20 (5.5 x 6.1)	28 (106)*	23.3 (161)	28 (106)**	23.3 (161)

*Centerline of the sprinkler located 4-3/8" (111mm) to 6-3/8" (162mm) below the ceiling.

**Centerline of the sprinkler located 6-3/8" (162mm) to 12-3/8" (314mm) below the ceiling.

Domed Concealed Pendent Sprinklers

Cover Plate Temp = 135°F /57°C; Adjustment up to 1/2" (13 mm)

4.9 (71) K-factor



VK468-D, Part No. 13637A-X
Technical datasheet F_020206

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	Horizontal Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	13 (49)	7.0 (48)
14 x 14 (4,3x4,3)	13 (49)	7.0 (48)
16 x 16 (4,9x4,9)	13 (49)	7.0 (48)
18 x 18 (5,5x5,5)	17 (64)	12.0 (83)
20 x 20 (6,1x6,1)	20 (76)	16.7 (115)

Upright Sprinklers

Available in 155°F/68°C and 175°F/79°C

4.9 (71) K-factor



VK467, Part No. 19154
Technical datasheet F_090413

- The industry's first and only residential upright sprinkler
- May provide significant design advantages in loft-type residential structures
- Listed with beam ceilings up to 14" (356 mm); deflector should be installed 1" - 3" below 14" beams
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	Flow gpm (lpm)	Horizontal Ceiling	
		Pressure psi (kPa)	Deflector to Ceiling
12 x 12 (3,7x3,7)	14 (53)	8.2 (56)	3-5" (76mm- 127mm)
14 x 14 (4,3x4,3)	14 (53)	8.2 (56)	
16 x 16 (4,9x4,9)	16 (61)	10.7 (73)	
12 x 12 (3,7x3,7)	15 (57)	9.4 (65)	*5-10" (127mm- 254mm)
12 x 12 (3,7x3,7)	15 (57)	9.4 (65)	
16 x 16 (4,9x4,9)	18 (68)	13.5 (93)	

*Note: Also applies to installations 1-3" below 14" beams at 155°F/68°C temperature rating only.

Viking offers lead-free versions of several Freedom® residential sprinklers. Please refer to Viking's technical datasheets for complete design and installation data.

Lead content complies with the definition of 'Lead Free' established in the Reduction of Lead in Drinking Water Act (S.3874) endorsed by AWWA's Water Utility Council, and California Assembly Bill #1953.

Horizontal Sidewall Sprinklers

Available in 155°F/68°C and 175°F/79°C; Recessed adjustment up to 5/8" (16mm)

3.0 (43) K-factor



VK479, Part No. 19707
Technical datasheet F_012915

- Sprinkler temp = 155°F/68°C
- Patented "flow shaper" design provides the ultimate combination of low flows and starting pressures
- Can optimize NFPA 13 residential designs when combined with larger K-factor residential sprinklers
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	4-12" (102mm-305mm) From Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	11 (42)	13.4 (92)
14 x 14 (4,3x4,3)	13 (49)	18.8 (129)
16 x 16 (4,9x4,9)	13 (49)	18.8 (129)

4.0 (58) K-factor



VK486, Part No. 17315
Technical datasheet F_082411

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Patented "flow shaper" design provides the ultimate combination of low flows and starting pressures
- Lowest flow rate in the industry
- Available with ENT plating (Nickel PTFE) for corrosion resistance

Coverage Area ft (m)	4-6" (102mm-152mm) From Ceiling		6-12" (152mm-305mm) From Ceiling	
	Flow gpm (lpm)	Pressure psi (kPa)	Flow gpm (lpm)	Pressure psi (kPa)
12 x 12 (3,7x3,7)	11 (42)	7.6 (52)	12 (46)	9.0 (62)
14 x 14 (4,3x4,3)	12 (46)	9.0 (62)	12 (46)	9.0 (62)
16 x 16 (4,9x4,9)	13 (49)	10.6 (73)	14 (53)	12.3 (85)
16 x 18 (4,9x5,5)	16 (61)	16.0 (110)	16 (61)	16 (110)
16 x 20 (4,9x6,1)	22 (83)	30.3 (209)	23 (87)	33.1 (228)
16 x 22 (4,9x6,7)	24 (91)	36.0 (248)	26 (98)	42.3 (291)
18 x 18 (5,5x5,5)	18 (68)	20.3 (140)	18 (68)	20.3 (140)
18 x 20 (5,5x6,1)	22 (83)	30.3 (209)	23 (87)	33.1 (228)
20 x 20 (6,1x6,1)	22 (83)	30.3 (209)	24 (91)	36.0 (248)

*Flows shown for 155°F/68°C; see technical datasheet for flows at 175°F/79°C.

4.2 (60) K-factor



VK484, Part No. 16240
Technical datasheet F_050310

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	13 (49)	9.6 (66)	14 (53)	11.1 (77)
14 x 14 (4,3x4,3)	14 (53)	11.1 (77)	16 (61)	14.5 (100)
16 x 16 (4,9x4,9)	16 (61)	14.5 (100)	18 (68)	18.4 (127)
16 x 18 (4,9x5,5)	19 (72)	20.5 (141)	20 (76)	22.7 (156)
16 x 20 (4,9x6,1)	22 (83)	27.4 (189)	25 (95)	35.4 (244)

*Flows shown for 155°F/68°C; see technical datasheet for flows at 175°F/79°C.

5.8 (84) K-factor



VK460, Part No. 13933
Technical datasheet F_110205

- Sprinkler temp = 155°F/68°C and 175°F/79°C
- Patented "flow shaper" design provides the ultimate combination of low flows and starting pressures
- Larger K-factor provides lower starting pressure in NFPA 13 applications (0.1 gpm/ft² density)
- Available with ENT plating (Nickel PTFE) for corrosion resistance

12 x 12 (3,7x3,7)	16 (61)	7.6 (52)	16 (61)	7.6 (52)
14 x 14 (4,3x4,3)	16 (61)	7.6 (52)	18 (68)	9.7 (67)
14 x 26 (4,3x7,9)	42 (159)	52.4 (362)	46 (174)	62.9 (434)
16 x 16 (4,9x4,9)	20 (76)	11.9 (82)	24 (91)	17.1 (120)
16 x 18 (4,9x5,5)	22 (83)	14.4 (99)	27 (102)	21.7 (149)
16 x 20 (4,9x6,1)	26 (98)	20.1 (139)	32 (121)	30.4 (210)
16 x 22 (4,9x6,7)	31 (117)	28.6 (197)	37 (140)	40.7(281)
16 x 24 (4,9x7,3)	38 (144)	42.9 (296)	42 (159)	52.4 (362)
18 x 18 (5,5x5,5)	23 (87)	15.7 (110)	29 (110)	25.0 (170)
18 x 20 (5,5x6,1)	29 (110)	25.0 (170)	35 (133)	36.4 (251)
20 x 20 (6,1x6,1)	30 (114)	26.8 (180)	36 (136)	38.5 (266)

*Flows shown for 155°F/68°C; see technical datasheet for flows at 175°F/79°C.

Flat Cover Plate Finishes

Freedom offers the smallest available cover plates and low-profile recessed sprinkler models, providing optimum protection while blending with décor. A choice of nine standard finishes and unlimited custom colors make Freedom almost undetectable once installed.

Viking concealed cover plates are UL Listed to accept any type and manufacturer of paint within the constraints of Viking's quality control requirements. All custom color painted cover plates have a label affixed to the inside of the cover that identifies the color by name, and that also carries a representative paint dot.

To order custom cover plate painting, contact your Viking SupplyNet customer service representative.



Our exclusive Colormatch® service can duplicate any paint sample or color chip, providing endless options for a beautiful, finished look.

Standard Finishes



Antique Brass



Brushed Chrome



White



Ivory



Bright Brass



Polished Chrome



Brushed Brass



Brushed Copper



Black

Custom Cover Plate Designs



Viking offers cULus Listed custom cover plate designs!

In addition to custom paint color options, Viking now offers custom designs.

Please visit webtools.vikingcorp.com/coverplates to submit a project request form.

Cover Plates

Technical datasheet Sprinkler F_040600



Standard

Thread on p/n 23190
Push on p/n 23447
2-3/4" (70 mm) diameter



Square

Thread on p/n 23179
Push on p/n 23482
3-5/16" (84 mm) L x W



Domed

Part No. 12207
3-1/8" (80mm) diameter



Large

Thread on p/n 23174
Push on p/n 23463
3-5/16" (84 mm) diameter

Recessed and Sloped Ceiling Escutcheons

Technical datasheet Sprinkler F_122698



- E-1 – Push-on, Part No. 11123-3/8", 06419-1/2", 20369-3/4"
- E-2 – Threaded, Part No. 11038-1/2", 20130-3/4"
- E-3 – Threaded, Part No. 18347-1/2", 18348-3/4"



- G-1 – Sloped, Part No. 14315-1/2"
Part No. 20133-3/4"
Push-on

Tools

Technical datasheet Sprinkler F_122598



Cabinet Wrench & Sprinkler Cap Removal Tool, Part No. 13619

(See Part No. 16267 for Models VK480 and VK490 and Part No. 14047 for Model VK494)



Concealed Cover Installer Tool, Standard Diameter, Part No. 14412

Concealed Cover Installer Tool, Large Diameter, Part No. 14867




Escutcheon Installer Tool, Part No. 15915 (Technical datasheet F_051808)



Individual tools and length of pipe all sold separately.

WARNING: Cancer and Reproductive Harm-
www.P65Warnings.ca.gov

Viking SupplyNet US and Canada Locations



Viking SupplyNet has thirty-one distribution centers in North America - fourteen with turn-key fabrication services.

Visit www.vikinggroupinc.com for a Viking SupplyNet location near you.