

BLUE LUBE PIPE GASKET LUBE GLP-SPEC

PRODUCT DESCRIPTION

PRODUCT

BLUE LUBE PIPE GASKET LUBE

TYPE

BLUE LUBE PIPE GASKET LUBE is a unique product that has been specially formulated to prevent turbidity, taste, and/or odor problems in new water main installations. **BLUE LUBE** will not promote bacterial growth.

RECOMMENDED USES

A blue viscous gasket lubricant for lubricating all rubber and plastic gaskets used in mechanical pipe coupling including Gruvlok* and Victaulic** type fittings. **BLUE LUBE** insures proper alignment of gaskets for correct fit during pipe installation. It works well on wet or dry surfaces and is nontoxic and suitable for use on potable water systems. Blue Lube is odorless and cleans up easily. Safe for use on all metal, plastic and rubber gasketed pipe.

COLOR/CONSISTENCY

Light Blue
Smooth, thixotropic lubricant.
Remains a paste at temperatures above 150°F (66°C). Will not break down if repeatedly frozen and thawed.

TEMPERATURE RANGE USE

0°F (-17°C) to 150°F (66°C)

CORROSIVENESS

Non-corrosive

FLAMMABILITY

Nonflammable

GLP-SPEC

*Anvil International Trademark
**Victaulic Co. Of America Trademark

© 2006 J.C. Whitlam Manufacturing Company
This product is manufactured in the U.S.A.

DRYING TIME

Drying time of the lubricant will vary with weather conditions; therefore, it is important to join the pipe and gasket as soon as possible after applying the lubricant. If drying should occur before joining the pipe with the gasket, re-swab the pipe and gasket immediately. For best results, apply with a cotton swab applicator.

PACKAGING

U.S. Measure:

Stock Code	Size
Plastic Container	
GLP16	1 pint (473 ml)
Plastic Container/Twist Top Lid	
GLP32	1 quart (.95 L)
Pail w/Handle	
GLP1	1 gal. (3.785 L)
GLP5	5 gal. (18.9 L)
55 Gallon Steel Drum	
GLP55	55 gal. (208 L)

WEIGHT PER U.S. GALLON

8.43 lbs. (3.82 kg) ±0.2

SHIPPING WEIGHT PER CASE


Stock#	Case Weight	#/Case
GLP16	30 lbs. (13.6 kg)	24/case
GLP32	28 lbs. (12.7 kg)	12/case
GLP1	37 lbs. (16.8 kg)	4/case
GLP5	45 lbs. (20.4 kg)	1 each
GLP55	500 lbs. (226.8 kg)	1 each




NSF Standard 14

NSF Standard 61


DIRECTIONS FOR USE




Step 1: Clean bell of pipe. Remove any loose dirt, gravel, rust, scale, or foreign material. Remove standing water for best results.




Step 2: Clean spigot of pipe as in Step 1. Surfaces must be thoroughly clean before application of "Blue Lube".



Step 3: Apply "Blue Lube" liberally to the bell of pipe. For best results use a cotton swab applicator.



Step 4: Apply "Blue Lube" liberally to the spigot of pipe. Keep the lubricated surfaces free from dirt.



Step 5: Immediately after application of the lubricant, assemble the joint. Apply even pressure and insert the spigot into the bell.

 **WHITLAM**
PLUMB-PRO
The Industry Standard for Over 100 Years

Division of
J.C. Whitlam Mfg. Company
P.O. Box 380
Wadsworth, Ohio 44282
Phone: 330-334-2524
Fax: 330-334-3005
email: info@jcwhitlam.com
website: www.jcwhitlam.com

The information contained in this bulletin is correct to the best of our knowledge. The recommendations or suggestions herein are made without guarantee or representation as to result, since the conditions of use are beyond our control. We suggest that you evaluate the recommendations contained in this bulletin. No statement is to be construed as violating any copyright or patent. They are intended only as a source of information.

recomm